

## Industrial Portable Cord



SteriGuard™ Antimicrobial Industrial Portable Cord provides excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of *Escherichia coli*, Gram (-) and *Staphylococcus aureus*, Gram (+) providing long-lasting benefits to manufacturers' beyond conventional cleaning methods. Industrial Portable Cord is manufactured using heavy-duty SEOW/STOW cord for maximum durability and longevity to meet the most demanding industrial and construction applications. SteriGuard provides a cost-effective way to add additional safety precautions and unequalled assurance that every feasible step has been taken in the interest of consumer protection. In addition, the SteriGuard™ Antimicrobial Industrial Portable Cord paired with SteriGuard™ Antimicrobial plugs and connectors are a complete antimicrobial solution.

## Features & Benefits



- **UL/CSA Listed**
- **Custom cords are engineered to order for desired length specifications** and NEMA type configurations
- **Patent Pending**

- **Antimicrobial Additives Embedded in polymer** and inhibits Growth of Bacteria, Molds, Mildews and Fungi
- **Antimicrobial Additive Resistant to Scuffing and Cleaning**
- **Escherichia (E.Coli):** Log reduction > 4.8, reduced surface bacteria by > 99.99%
- **Staphylococcus (Staph), MRSA:** Log Reduction > 4.3, reduces surface bacteria by > 99.97%
- **Salmonella:** Log Reduction > 3.6, reduces surface bacteria by > 99.97%
- **RoHS Compliant (Non-Halogenated)**
- **Independently tested and Certified to JIS Z2801 standards**
- **Resistant to High Pressure Hose-down applications**
- **Tongue & Groove Environmental Sealing**
- **Keyed Body and Cover for Alignment**
- **NEMA Type 4, 4x, 6, 6P and IP67 Protection**
- **Additives are embedded** in both the cord and wiring devices
- **SteriGuard™ Antimicrobial Industrial Portable Cord is ideal for a wide range of applications** including food and beverage preparation, procession, & packaging; agriculture, pharmaceutical and health care

## Compliance



UL Listed, Standard UL498 (Plug/Connector). CSA Certified, Standard CSA C22.2 No. 42. Conforms to NEMA WD-1, WD-6 and ANSI standards. NSF certification.

---

## Technical Information

### Specifications

---

#### General Information

---

Type	Cord
Special Features	Straight, Locking, Watertight, NEMA

---

#### Listing Agencies/Third Party Information

---

CSA Listing Info	C22.2 No. 42M
CSA Listed	Yes
cUL Standard	Yes
UL Listing No	UL498
UL Listed	Yes
UL Standard	Yes
UN SPS C	39121402

---

#### Cord Information

---

Cord Length (US)	12/3, 12/4, 10/4 SEOW/STOW, Consult your Legrand rep for additional construction sizes
------------------	--

---

#### Technical Information

---

Material	Thermoplastic Elastomer/ Rubber
Operating Temperature Celsius	-50°C- 150°C
Volts	600V

---

#### Buy American Act Compliance

---

Country of Origin	UNITED STATES OF AMERICA
Buy American Act Status	Buy American Act Compliant

---

---

## Ordering Information

### SteriGuard Bulk Cord Sets

<b>P&amp;S Part #</b>	<b>Description</b>
<b>PS14350AM</b>	14/3 SEOW/STOW Bulk Cord 50'
<b>PS143100AM</b>	14/3 SEOW/STOW Bulk Cord 100'
<b>PS1431000AM</b>	14/3 SEOW/STOW Bulk Cord 1000'
<b>PS12350AM</b>	12/3 SEOW/STOW Bulk Cord 50'
<b>PS123100AM</b>	12/3 SEOW/STOW Bulk Cord 100'
<b>PS1231000AM</b>	12/3 SEOW/STOW Bulk Cord 1000'
<b>PS12450AM</b>	12/4 SEOW/STOW Bulk Cord 50'
<b>PS124100AM</b>	12/4 SEOW/STOW Bulk Cord 100'
<b>PS1241000AM</b>	12/4 SEOW/STOW Bulk Cord 1000'