

Electronic Thermostats



Mechanical Thermostats



Electronic Thermostats

Product #	Description
TH114-A-024T-15S	Non programmable electronic low voltage thermostat (15-second cycle) 0.5A at 24V
TH114-AF-024T	Non programmable electronic low voltage thermostat (15-minute cycle) 0.5A at 24V
TH115-AF-024T/U	Programmable electronic low voltage thermostat (15-minute cycle) 0.5A at 24V
TH115-A-024T-15S ¹	Programmable electronic low voltage thermostat (15-second cycle) 0.5A at 24V
TH5220D1003	Non programmable, electronic, heat/cool, low voltage thermostat (up to 2 heat/2 cool), 0.5A at 24V
TH6220D1002	Programmable, electronic, heat/cool, low voltage thermostat (up to 2 heat/2 cool), 0.5A at 24V

¹ Floor sensor not included.
Standard color is white.

Double-Pole Line Voltage Electronic Thermostat

Product #	Watts	Volts	Amp	Description
TH114-A-240D	3600	240/208	15	Non programmable electronic double-pole line voltage thermostat

Standard color is white.

Non programmable line voltage electronic thermostat

Product #	Watts	Volts	Description
TL116	1500/2600/3000	120/208/240	Non programmable line voltage electronic thermostat

Standard color is white.

Mechanical Low Voltage Thermostats

Product #	Description
T87K1015	Mechanical low voltage thermostat, round 10 °C to 35 °C
T822K1034	Mechanical low voltage thermostat, rectangular, 10 °C to 32 °C

Standard color is white.

Mechanical Line Voltage Thermostats

Product #	Description	Temperature
OTL101C	Mechanical line voltage thermostat, single-pole, single-throw, 19A at 277V, 22A at 120/208/240V	5 °C to 25 °C
OTL101F	Mechanical line voltage thermostat, double-pole, single-throw, 19A at 277V, 22A at 120/208/240V	41 °F to 80 °F
OTL102C	Mechanical line voltage thermostat, double-pole, single-throw, 19A at 277V, 22A at 120/208/240V	5 °C to 25 °C
OTL102F	Mechanical line voltage thermostat, double-pole, single-throw, 19A at 277V, 22A at 120/208/240V	41 °F to 80 °F
T498A1927	Mechanical line voltage thermostat, single-pole, single-throw, 19A at 277V, 22A at 120/208/240V	5 °C to 25 °C

Standard color is white.

Programmable Battery-Powered Electronic Thermostat (Low or Line Voltage)

Product #	Amp.	Volts	Description
TH140-28-01-B	5A (resistive) 2A (inductive)	24/120/240	Programmable battery-powered electronic thermostat

Standard color is white.