

BP320 Series


320 A 600 V self-contained meter socket

Product specifications overhead

- 320 A overhead 600 V maximum
- Self-contained meter socket with bypass mechanism
- Single-phase service
- Line and load side termination; tunnel type connectors; dual rated for 1 x 500 kcmil or 2 x 250 kcmil
- Neutral termination; tunnel type connectors; dual rated 2 x 250 kcmil
- Supplied with screw type sealing ring
- Weatherproof type 3R enclosure
- Primarily used in: All provinces

Product specifications underground

- 320 A underground 600 V maximum
- Self-contained meter socket with bypass mechanism
- Single-phase service
- Neutral and line side terminations; double ½ in. studs to accommodate compression lugs for underground service (1 x 500 kcmil or 2 x 250 kcmil)
- Load side terminations; tunnel type connectors; dual rated for 1 x 500 kcmil or 2 x 250 kcmil
- Neutral load side terminations; tunnel type connectors; dual rated 2 x 250 kcmil
- Supplied with screw type sealing ring
- Weatherproof type 3R enclosure
- Primarily used in: All provinces



Cat. no.	Type	Description	Color	Position	Dimensions (in.)			Weight each	
					H	W	D	lb	kg
BP320-V	Overhead	Overhead 320 A 120/240 V with bypass mechanism	Grey	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-V-250	Overhead	320 AMP 120/240 with bypass mechanism with 2 x 250 kcmil lugs	Grey	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-V-08	Overhead	Overhead 320 A 120/240 V with bypass mechanism	Dark Grey	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-V-09	Overhead	Overhead 320 A 120/240 V with bypass mechanism	White	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-V-11	Overhead	Overhead 320 A 120/240 V with bypass mechanism	Beige	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-TV	Underground	Underground 320 A 120/240 V with bypass mechanism	Grey	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-TV-250	Underground	320 AMP 120/240 v with by pass mechanism comes with 2 x 250 kcmil lugs	Grey	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-TV-08	Underground	Underground 320 A 120/240 V with bypass mechanism	Dark Grey	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-TV-09	Underground	Underground 320 A 120/240 V with bypass mechanism	White	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31
BP320-TV-11	Underground	Underground 320 A 120/240 V with bypass mechanism	Beige	1	34 ³ / ₁₆	15 ⁹ / ₁₆	5 ¹⁵ / ₁₆	47	21.31

Accessory

BP250

BP250


Connector kit 2 x 250 kcmil




BP320 Series

320 A 600 V self-contained meter socket

Diagrams



Overhead



Underground