

Cable Knives

Cable/Lineman's Skinning Knives

- Cat. Nos. 1570-3 and 1570-3LR feature three-inch steel blades that withstand frequent scoring and slitting of cable jacket
- Notch on blade back for scraping or removing wire insulation
- Comfortable textured handle with finger grooves and guard
- No contact between stainless steel ring and hardened steel blade (Cat. No. 1570-3)
- Rectangle-shaped handle design for attachment to some utility hot stick equipment
- Leather sheath available, Cat. No. 5163 only for Cat. Nos. 1570-3 and 1570-3LR
- Cat. No. 1580-3 has a 2" (50.8 mm) blade for increased control when scoring and slitting cable jacket and an ergonomic handle for maximum comfort



Cat. No.	Special Features	Blade Length	Overall Length	Blade Material	Handle Color	Weight
1570-3	Hook Blade, Notch, and Ring	3" (76.2 mm)	8" (203.2 mm)	Steel	Black	4.8 oz (136 g)
1570-3LR	Hook Blade and Notch	3" (76.2 mm)	8" (203.2 mm)	Steel	Black	4.6 oz (130 g)
1580-3	Hook Blade, Notch, and Ring	2.047" (52 mm)	8.75" (222.3 mm)	Steel	Black	4.5 oz (128 g)

Cable-Sheath Splitting Knife

- Compact, lightweight knife for opening lead cables
- Rugged, forged tempered cutlery steel blade
- Sharp chisel-shaped edge
- Hammer head on back
- Plastic-dipped handles for comfort
- Leather guard available, Cat. No. 5574S



Cat. No.	Blade Length	Overall Length	Weight
1515-S	2.75" (69.9 mm)	7.375" (187.3 mm)	0.35 lb (0.16 kg)


Bell System Cable-Sheath Splitting Knife - Heavy-Duty

- Heavy-duty knife for splitting cable sheaths
- Rugged, forged tempered cutlery steel blade
- Sharp chisel-shaped edge
- Plastic-dipped handles for comfort
- Leather guard available, Cat. No. 5574L



Cat. No.	Blade Length	Overall Length	Weight
1515-1	4.5" (114.3 mm)	9" (228.6 mm)	1.2 lb (0.5 kg)





Cable Knives

Cable-Splicer's Knife

- Special-purpose short blade with comfortable, full-sized, heavy-duty handle
- Coping-type blade made of the finest cutlery steel, tough and carefully tempered to hold its edge
- Handle is textured for comfort and firm grip
- Hang hole for easy storage and portability



44200

Cat. No.	Blade Length	Overall Length	Weight
44200	1.75" (44.5 mm)	6.25" (158.8 mm)	0.15 lb (0.07 kg)

Cable-Splicer's Kits

- Cuts cable, telephone wire, and strips insulation
- Dimensions: 2-1/8" (54 mm) x 7-1/2" (190.5 mm)

Cat. No.	Kit Contains	Weight
46037	Cable Splicer's Kit	8.0 oz (227 g)
Cat. No.	Description	
44200	Cable Splicer's Knife, 6-1/2"	
2100-7	Electrician's Scissors, Nickel Plated	
5187	Scissors and Cable Splicer's Knife Holder	
Cat. No.	Kit Contains	Weight
46039	Cable Splicer's Kit with Free-Fall Snip	9.3 oz (264 g)
Cat. No.	Description	
44200	Cable Splicer's Knife, 6-1/2"	
21010	Free-Fall Snip	
5187	Scissors and Cable Splicer's Knife Holder	



46037

46039

Specialty Knife

Serrated Duct Knife

- Cuts duct board and flexible duct.
- Double-edged knife - regular and serrated.
- Cushion-grip handle for comfort.
- Includes puncture resistant nylon sheath with belt loop.



DK06

Cat. No.	Blade Length	Blade Material	Weight
DK06	5.5" (139.7 mm)	Stainless Steel	8.5 oz (241 g)

See page 297 for additional information on warnings.



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. **Check local laws on legality of selling or possessing these knives.**

Sharpening Tools

Pocket-Sized Knife Sharpener

- Versatile sharpener featuring fine craftsmanship and unique design
- Sharpening rod unscrews and stores in handle for convenient carrying in tool box, pouch, or pocket
- Sharpening rod is precision-cut, hard-chromed steel for accurate, consistent sharpening and long life
- Magnetized to trap metal particles when sharpening
- Handle is a high-visibility orange color with handy pocket clip

PRODUCT SHOWN CLOSED



PRODUCT SHOWN OPEN

44151

Cat. No.	Blade Length	Overall Length	Overall Width	Blade Material	Handle Length	Weight
44151	3.75" (95.3 mm)	9.5" (241.3 mm)	0.5" (12.7 mm)	Steel	5.5" (139.7 mm)	0.80 oz (22.7 g)

Combination Knife and Scissors Sharpener

- High-grade, tungsten-carbide inserts sharpen both sides of the blade at the same time
- Restores knife edge in three or four strokes
- Built-in finger guard helps to protect your hand
- Lightweight, compact size for easy carrying and storage
- Sharpens electrician's scissors, pocket knives, retractable-blade utility knives, razor blade knives and serrated knives



48036

Cat. No.	Overall Length	Overall Width	Weight
48036	4" (101.6 mm)	2.25" (57.2 mm)	0.10 lb (0.05 kg)

WARNING: Improper use of knife and scissors sharpener and/or failure to follow instructions can result in injuries. Keep your fingers behind the curved guard and your thumb securely on the multi-grooved thumb-rest indentation, never in front of it.

Electrician's Scissors

Electrician's Scissors

- Nickel plated to resist corrosion (Cat. Nos. 2100-5 and 2100-7)
- Notches for stripping 19 AWG and 23 AWG wire on the upper blade (Cat. Nos. 2100-7, 2100-8 and 2100-9)
- Extended handle to provide comfort and cutting leverage (Cat. No. 2100-8)



2100-8



2100-7



2100-5



2100-9

Cat. No.	Special Features	Application	Material	Cutting Length	Overall Length	Weight
2100-5	Scraper, File	Telecom, Electrical, Heavy-Duty Cutting	Steel	1.875" (47.6 mm)	5.25" (133.4 mm)	0.20 lb (0.09 kg)
2100-7	Scraper, File, Stripping Notches, Serrated Blades	Telecom, Electrical, Heavy-Duty Cutting	Steel	1.875" (47.6 mm)	5.25" (133.4 mm)	0.20 lb (0.09 kg)
2100-8	Free-Fall Snip, Extended Handle, Serrated Blades	Wire Cutting; Stripping	Stainless Steel	1.875" (47.6 mm)	6.313" (160.4 mm)	0.21 lb (0.10 kg)
2100-9	Free-Fall Snip, Serrated Blades	Wire Cutting; Stripping	Stainless Steel	1.875" (47.6 mm)	5.25" (133.4 mm)	0.21 lb (0.10 kg)

WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. Check local laws on legality of selling or possessing these knives.

