

2-120-T Aurora MR16



With a myriad of reflector, trim, and color temperature combinations, Aurora blends discretely with any décor. The 2 1/2" regressed lamp delivers high lumens without glare, while 35° aiming increases flexibility in locating luminaires.

FEATURES

- Utilizes MR16
- 35° aiming
- Die-cast aluminum fixture
- Powder coated and plated trim ring finishes
- Trim clips designed for 5/8" ceiling thickness
- Accepts up to 2 optional media
- Clear glass lens included
- Trimless version available (see separate specifications)

DETAILS

Trim Class: 4"
Category: Recessed Downlight
Shape: Round
Adjustability: Aiming




2-120-T-Aurora-MR16-Specs • Subject to change without notice • Rev 2016.12.19 • 1/4


Compatible Housings

NON-INSULATED

2-020
Round Non-Insulated
L 10 1/2" [267mm]
W 7 3/4" [197mm]
H 3 1/2" [90mm]




2-060
Round Non-Insulated
L 13 3/4" [349mm]
W 10 7/8" [276mm]
H 3 1/2" [90mm]




INSULATED

2-010
Round Insulated
L 13 3/4" [350mm]
W 10 7/8" [277mm]
H 7" [178mm]




2-012
Round Insulated
L 22 1/2" [572mm]
W 8 1/2" [216mm]
H 5 7/8" [150mm]




REMODEL

2-030
Round Remodel
L 14" [356mm]
W 4 1/2" [114mm]
H 5 1/8" [130mm]




SPECIALIZED

2-060
Round Chicago Plenum
L 13 3/4" [350mm]
W 10 7/8" [277mm]
H 4 1/2" [115mm]



2-100
Round Concrete Housing
L 18" [457mm]
W 12" [305mm]
H 6" [152mm]



2-120-T Aurora MR16

Project

Type

Notes

Product Code

1 2 3 4

1. Trim

2-120-T Aurora

2. Lamp

MR16 Halogen

3. Flange Finish

01 White

02 Chrome Plated

04 Black

05 Matte Silver

06 Bronze

09 Gold Plated

11 Matte Nickel

CC Custom Color¹

4. Reflector Finish

BLO Black Open

BA Black Specular

BLS Black Stepped Baffle

CHA Champagne Specular

CHAS Champagne Satin

COPA Copper Specular

COPAS Copper Satin

GA Gold Specular

GAS Gold Satin

MOCH Mocha Brushed

NICS Nickel Satin

SA Silver Specular

SAS Silver Satin

WHO White Open

WHS White Stepped Baffle

Notes

¹ **CC** custom color requires consultation with Lightheaded sales personnel.

2-120-T-Aurora-MR16-Specs • Subject to change without notice • Rev 2016.12.19 • 4/4