



VersaMATE®

Features:

The VersaMate® product line includes 30, 60, 100, 150 and 200 Amp plugs, receptacles and connectors with a full range of back boxes. Popular options include reverse service and polarization. The VersaMate line is FULLY INTERCHANGEABLE with UL1686 configured and listed devices such as Crouse-Hinds® Arktite® or Appleton® Powertite®. Standard location receptacle bolt hole patterns match competitive back boxes so users can upgrade to VersaMate without changing back boxes in instances where changing the conduit system is difficult.

PLUGS

30AMP	
VP3034-S39	30A 3W4P PLUG ASSY. - REVERSE SERVICE AT
VP3044-S39	30A 4W4P PLUG ASSY. - REVERSE SERVICE AT
VP3475	30A 4W4P PLUG STYLE I
VP3485	30A 3W4P PLUG STYLE II
60AMP	
VP6034-S39	60A 3W4P PLUG ASSY. - REVERSE SERVICE AT
VP6375	60A 3W3P PLUG STYLE I
VP6475-S39	60A 4W4P PLUG REVERSE SERVICE
VP6485	60A 3W4P PLUG STYLE II
100AMP	
VP1034-S39	100A 3W4P PLUG ASSY. - REVERSE SERVICE AT
VP10477-S39	100A 4W4P REVERSE SERVICE
VP10487	100A 3W4P PLUG STYLE II
VP10487-S39	100A 3W4P PLUG ASSY REVERSE SERVICE
150AMP	
VPA15034	150A 3W4P PLUG ASSY
200AMP	
VP204612	200A 3W4P PLUG
VP204612-S39	200A 3W4P PLUG ASSY

RECEPTACLES

30AMP	
VR341	30A 4W4P RECEPTACLE STYLE I
VR342	30A 3W4P RECEPTACLE STYLE II
60AMP	
VR631	60A 3W3P RECEPTACLE STYLE I
VR641	60A 4W4P RECEPTACLE STYLE I
VR641-S39	60A 4W4P RECEPTACLE REVERSE SERVICE
VR642	60A 3W4P RECEPTACLE STYLE II
100AMP	
VR1041	100A 4W4P RECEPTACLE STYLE I
VR1041-S39	100A 4W4P RECEPTACLE REVERSE SERVICE
VR1042	100A 3W4P RECEPTACLE STYLE II
VR1042-S39	100A 3W4P RECEPTACLE REVERSE SERVICE
150AMP	
VRA15034	150A 3W4P RECEPTACLE ASSY
200AMP	
VR20422	200A RECEPTACLE 3W4P

BACK BOX

30AMP	
VRE23	BACK BOX E-TYPE 3/4" 30A
60AMP	
VRE36	BACK BOX E-TYPE 1" 60A
VRE46	BACK BOX E-TYPE 1-1/4" 60A
100AMP	
VJ47	VERSA MATE 100A 1-1/4" BACK BOX
VJ57	BACK BOX E-TYPE 1 1/2" 100AMP
200AMP	
VJ68	BACK BOX E-TYPE 1 1/2" 200AMP