


Dimensions

NAME	PART NUMBER	DIMENSIONS (H x W x D)
Paddle Switch	ASPD1531W4	1.77" x 1.77" x 1.5"
	ASPD1532M4	1.77" x 1.77" x 1.59"
	ASPD2032W4	1.77" x 1.77" x 1.59"
	ASPD2032M4	1.77" x 1.77" x 1.72"
	ASPD2042W4 ASPD2042M4	1.77" x 1.77" x 1.72"
Paddle Dimmer	ADPD703HW4	4.20" x 1.77" x 1.62"
	ADPD703HM4	4.20" x 2.51" x 1.62"
	ADPD1103HW4	4.20" x 2.51" x 1.62"
	ADPD1103HM2	4.20" x 1.77" x 1.62"
	ADPD453LW2 ADPD453LM2	4.20" x 1.77" x 1.62"
Paddle Switch, Half-Size	ASPD1531W4 ASPD1531M4	1.77" x 0.89" x 1.5"
Paddle Fan Speed Control	AAFN4S16AW4 AAFN4S16AM4	2.66" x 1.77" x 1.85"
Whisper Switch	ASWR1532W4 ASWR1532M4	1.77" X 1.77" x 1.63"
Whisper Wi-Fi Ready Switch	ADWR703HM4	1.77" X 1.77" x 1.63"
	ADWR703HW4	1.77" X 1.77" x 1.63"
	ADWR1103HW4 ADWR1103HM4	1.77" X 1.77" x 1.63"
Whisper Dimmer	ADWR703HW4	4.20" x 1.77" x 1.77"
	ADWR703HM4	4.20" x 2.51" x 1.77"
	ADWR1103HW4 ADWR1103HM4	4.20" x 2.51" x 1.77"
Whisper Wi-Fi Ready Dimmer	ADWR600RMHW1	4.20" x 1.77" x 1.79"
	ADWR600RMHM1	4.20" x 1.77" x 1.79"
	ADWR700RMTUW1	4.20" x 1.77" x 1.79"
	ADWR700RMTUM1 ADWRRRW1 ADWRRRM1	4.20" x 1.77" x 1.79"
sofTap Switch	ASTP1532W4 ASTP1532M4	2.66" x 1.77" x 1.63"
sofTap Dimmer	ADTP703HW2	4.20" x 1.77" x 1.79"
	ADTP703HM2	4.20" x 2.51" x 1.79"
	ADTP1103HW4	4.20" x 2.51" x 1.79"
	ADTP1103HM4 ADTP703UW2 ADTP703UM2	4.20" x 1.77" x 1.79"
sofTap Wi-Fi Ready Switch	ASTPRF2W2	2.66" x 1.77" x 1.63"
	ASTPRF2M2	2.66" x 1.77" x 1.63"
	ASTPRFR2W2 ASTPRFR2M2	2.66" x 1.77" x 1.63"
sofTap Wi-Fi Ready Switch	ASTP155RMW1	2.66" x 1.77" x 1.63"
	ASTP155RMM1 ASTPRRW1 ASTPRRM1	2.66" x 1.77" x 1.63"
sofTap Wi-Fi Ready Dimmer	ADTP700MMUW2	4.20" x 1.77" x 1.79"
	ADTP700MMUM2	4.20" x 1.77" x 1.79"
	ADTP700MMHW2	4.20" x 1.77" x 1.79"
	ADTP700MMHM2 ADTPMRUW2 ADTPMRUM2	4.20" x 1.77" x 1.79"
sofTap Wi-Fi Ready Dimmer	ADTP700RMHW1	4.20" x 1.77" x 1.79"
	ADTP700RMHM1	4.20" x 1.77" x 1.79"
	ADTP700RMUW1	4.20" x 1.77" x 1.79"
	ADTP700RMUM1 ADTPRRW1 ADTPRRM1	4.20" x 1.77" x 1.79"

NAME	PART NUMBER	DIMENSIONS (H x W x D)
Push Switch	ASPU1532W4 ASPU1532M4	1.77" X 1.77" x 1.82"
SensaSwitch, Auto-ON/ Auto-OFF	ASOS32W4 ASOS32M4	2.66" x 1.77" x 1.85"
SensaSwitch, Manual- ON/Auto-OFF	ASVS12W4 ASVS12M4	2.66" x 1.77" x 1.85"
SensaSwitch, Manual- ON/Timed-OFF	ASTM2W2 ASTM2M2	2.66" x 1.77" x 1.85"
SensaDimmer, Auto- ON/Auto-OFF	ADSM703HW2 ADSM703HM2	4.20" x 1.77" x 1.85"
Wave Switch	ASWV1532W2 ASWV1532M2	2.66" x 1.77" x 1.71"
Touch Switch	ASTH1532W2 ASTH1532M2	2.66" x 1.77" x 1.63"
Touch Wi-Fi Ready Switch	ASTH155RMW1	2.66" x 1.77" x 1.63"
	ASTH155RMM1	2.66" x 1.77" x 1.63"
	ASTHRRW1 ASTHRRM1	2.66" x 1.77" x 1.63"
Touch Wi-Fi Ready Dimmer	ADTH700MMUW2	4.20" x 1.77" x 1.79"
	ADTH700MMUM2	4.20" x 1.77" x 1.79"
	ADTHMRUW2	4.20" x 1.77" x 1.79"
	ADTHMRUM2 ADTH700RMHW1 ADTH700RMHM1 ADTH700RMUW1 ADTH700RMUM1 ADTHRRW1 ADTHRRM1	4.20" x 1.77" x 1.79"
Blank, Half-Size	AABK1W4 AABK1M4	1.77" X 0.89" x 0.96"
Tamper-Resistant Outlet	ARTR152W4	2.12" x 1.77" x 1.73"
	ARTR152M4	2.12" x 1.77" x 1.73"
	ARTR202W4 ARTR202M4	2.12" x 1.77" x 1.73"
Tamper Resistant Outlet, Plus-Size	ARTR153W4 ARTR153M4	3" x 1.77" x 1.48"
Tamper-Resistant GFCI	AGFTR152W4	2.66" x 1.77" x 1.82"
	AGFTR152M4	2.66" x 1.77" x 1.82"
	AGFTR202W4 AGFTR202M4	2.66" x 1.77" x 1.82"
Tamper-Resistant GFCI, Plus-Size	AGFTR153W4 AGFTR153M4	3.00" x 1.76" x 1.82"
Energy-Saving ON/OFF Outlet	ARPS152W4 ARPS152M4	2.66" x 1.77" x 1.73"
Wi-Fi Ready Outlet	ARPS15RF2W4 ARPS15RF2M4	2.66" x 1.76" x 1.82"
USB Outlet, Half-Size	ARUSBW4 ARUSBM4	1.77" X 0.89" x 1.81"



Pop-Out™ Outlet (Receptacle)

Pop-Out Outlets require a special frame (included in package) and are not compatible with those used with adorne wall plates. **They require a deep box, such as Pass & Seymour SI22R, for installation or in a location that has a thick material like a kitchen backsplash, in a standard box.** Each outlet includes capacity for three plugs.

NAME	DESCRIPTION	RATINGS	NEMA CONFIGURATION	COMPLIANCE	FINISH OPTIONS	PART NUMBER
Pop-Out Outlet, 1-Gang	Includes 1-gang frame for installation. Cannot be paired with other switches, dimmers, outlets, or accessories. 15A version provides 3 receptacles. 20A version provides 2 receptacles.	15A	5-15R		White Magnesium	ARPTR151GW2 ARPTR151GM2
		20A	5-20R		White Magnesium	ARPTR201GW2 ARPTR201GM2
Pop-Out Outlet, 2-Gang	Includes one Pop-Out Outlet and 2-gang frame for installation. Select this option to pair your Pop-Out Outlet with another adorne switch, dimmer, outlet, or accessory.	15A	5-15R		White Magnesium	ARPTR152GW2 ARPTR152GM2

