Technical Information Bulletin



LED Puck Light ____

Date:	Name of distributor:
In hands date of project:	Client #:
Project name/Number:	Name of end user:

ORDERING INFORMATION

Order code: 67170

Description: UCP/12V/2.2W/40K/FR/WH/STD

UPC: 69549671706

Case quantity:

PHYSICAL DATA

Type: LED Puck Light

Size (in): 3" Shape: Round Finish: White Lens Finish: Frosted

Mounting: Surface and Recessed

Wire Length (ft.): Wire gauge (AWG): 24

Daisy Chain installation: Up to 10 pucks can be installed in daisy chain

PERFORMANCE DATA

Watts (W): 2.2 Volts (VDC): 12 Colour temp. (K)1: 4 000 Lumen output (lm): 150 Lumen per Watts (Im/W): 68 90 Life L70 (h)2: 50 000 Beam angle (°):

Operating temp. range: -20°C to 40°C (-4°F to 104°F)

 $^{^1}$ Typical colour temperature range: +/- 5 % 2 Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations













COMPATIBLE ACCESSORIES

Older Code	Description	туре
67181	UCP/TRIM/BACKPLATE/BLK/STD	Black trim and back plate
67182	UCP/TRIM/BACKPLATE/BN/STD	Brushed nickel trim and back plate
67183	UCP/ACC/HUB6/STD	Hub for 6 LED Puck Lights
67185	7185 UCP/ACC/DIMMER/STD Dimmer Switch	
67186	LICP/ACC/MOTIONSENSOR/STD	Motion Sensor

TECHNICAL DRAWINGS AND DIMENSIONS







COMPATIBLE DRIVERS

Order code	Description	
67184*	LED/DRIVER/12W/12V/PLUG/ND/STD	*(Included in the kits of 3 units)
62265	LED/TAPE/36W/12V/WW+CW/PS/ND/STD	,
65743	LED/DRIVER/10W/12V/HW/ND/STD	
65744	LED/DRIVER/20W/12V/HW/ND/STD	
65740	LED/DRIVER/50W/12V/HW/D/STD	
65745	LED/DRIVER/60W/12V/HW/ND/VS/STD	
65746	LED/DRIVER/60W/12V/HW/ND/STD	
67071	DRIVER-DIMMER/12V/60W/WH/STD	

DESCRIPTION AND OTHER OPTIONS

	UCP	/	12V	/	2.2W	/	40K	/	FR	/	WH	/	STD
	Family		Volts		Watts		Colour Temperature		Lens Finish		Trim Colour		Brand
UCP	Undercabinet Pucks		12V 12 Volts		2.2W 2.2 Watts		30K 3 000 K 40K 4 000 K		FR Frosted		WH White BLK Black BN Brushed nickel		STD STANDARD

Qiy	Description	rice	
I accept the spe	ecifications of the luminaire configuration men	lioned above.	
Name:			
Company:			
Signaturo:		Date:	