Technical Information Bulletin



LED Puck Light ____

Date:	Name of distributor:	
In hands date of project:	Client #:	
Project name/Number:	Name of end user:	

ORDERING INFORMATION

Order code: 67177

UCP/KIT3/12V/2.2W/30K/FR/BN/STD **Description:**

UPC: 69549671775

Case quantity:

PHYSICAL DATA

Type: LED Puck Light - kit of 3 units

Size: Shape: Round

Finish: Brushed nickel Lens Finish: Frosted

Surface and Recessed Mountina:

Wire Length (ft.): Wire gauge (AWG): 24

Daisy Chain installation: Up to 10 pucks can be installed in daisy chain

PERFORMANCE DATA

Watts (W) per unit: 2.2 Volts (VDC): 12 3 000 Colour temp. (K)1: Lumen output (lm) per unit: 150 Lumen per Watts (Im/W) per unit: 68 90 50 000 Life L70 (h)2: Beam angle (°): 120

Operating temp. range: -20°C to 40°C (-4°F to 104°F)

 $^{^{\}rm I}$ Typical colour temperature range: +/- 5 % $^{\rm 2}$ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations












COMPATIBLE ACCESSORIES

Order code	Description	Туре				
67180	UCP/TRIM/BACKPLATE/WH/STD	White trim and back plate				
67181	UCP/TRIM/BACKPLATE/BLK/STD	Black trim and back plate				
67183	UCP/ACC/HUB6/STD	Hub for 6 LED Puck Lights				
67185	UCP/ACC/DIMMER/STD	CC/DIMMER/STD Dimmer Switch				
47194	LICP/ACC/MOTIONSENSOP/STD	Motion Sensor				

TECHNICAL DRAWINGS AND DIMENSIONS







COMPATIBLE DRIVERS

Order code Description

		_
67184*	LED/DRIVER/12W/12V/PLUG/ND/STD	*(Included in the kits of 3 units)
62265	LED/TAPE/36W/12V/WW+CW/PS/ND/STD]
65743	LED/DRIVER/10W/12V/HW/ND/STD	
65744	LED/DRIVER/20W/12V/HW/ND/STD	
65740	LED/DRIVER/50W/12V/HW/D/STD	
65745	LED/DRIVER/60W/12V/HW/ND/VS/STD	
65746	LED/DRIVER/60W/12V/HW/ND/STD	
67071	DRIVER-DIMMER/12V/60W/WH/STD	1

DESCRIPTION AND OTHER OPTIONS

UCP	/	KIT3	/	12V	/	2.2W	/	30K	/	FR	/	BN	/	STD
Family		Kit		Volts		Watts		Colour Temperature		Lens Finish		Trim Colour		Brand
UCP Undercabinet Pucks		3 Kit of 3		12V 12 Volts		2.2W 2.2 Watts		30K 3 000 K 40K 4 000 K		FR Frosted		WH White BLK Black BN Brushed nickel		STD STANDARD

Qty		Description	Price							
I accept the spe	accept the specifications of the luminaire configuration mentioned above.									
Name:										
Company:										
Signature:			Date:							