

# REDLITHIUM™

## HIGH OUTPUT™

**50%  
MORE POWER  
& RUNS COOLER**  
VS REDLITHIUM™



## UPGRADING THE PERFORMANCE OF THE ENTIRE M18™ SYSTEM

M18™ REDLITHIUM™ HIGH OUTPUT™ Batteries deliver more power and run cooler, while providing more run-time and faster charging vs. their M18™ REDLITHIUM™ counterparts. This allows users to experience faster application speeds and greater productivity in all three segments of M18™ Batteries (CP, XC, and HD), under one fully compatible system.

### HIGH OUTPUT™ HD

The most power and run-time of all batteries. True corded and gas replacement, with ideal performance for high demand applications and tools.




### HIGH OUTPUT™ XC

More power and run-time versus compact batteries, with a great balance of performance and weight for a wide variety of tools and applications.



### HIGH OUTPUT™ CP

Powerful, with less weight and smaller size for reduced user fatigue and a better fit in tight spaces. Perfect for overhead work, and lightweight tools with users desiring XC power in a compact size.



## M18™

**PERFORMANCE DRIVEN  
TRADE FOCUSED  
SYSTEM WIDE**



### FITS M18™ TOOLS



**BEST PERFORMANCE FOR HIGH DEMAND APPLICATIONS**



**HIGH OUTPUT™**  
**48-11-1812**  
M18™ REDLITHIUM™  
HIGH OUTPUT™  
HD12.0 Battery Pack



**48-11-1890**  
M18™ REDLITHIUM™  
HD9.0 Battery Pack



**MORE POWER AND RUN-TIME; GREAT PERFORMANCE FOR ALL DEMANDS**



**HIGH OUTPUT™**  
**48-11-1880**  
M18™ REDLITHIUM™  
HIGH OUTPUT™  
XC8.0 Battery Pack

**NEW**



**HIGH OUTPUT™**  
**48-11-1865**  
M18™ REDLITHIUM™  
HIGH OUTPUT™  
XC6.0 Battery Pack  
**48-11-1862**  
2-Pack



**48-11-1850**  
M18™ REDLITHIUM™  
XC5.0 Battery Pack  
**48-11-1852**  
2-Pack



**48-11-1828**  
M18™ REDLITHIUM™  
XC3.0 Battery Pack  
**48-11-1822**  
2-Pack



**LESS WEIGHT AND SMALLER SIZE**



**HIGH OUTPUT™**  
**48-11-1835**  
M18™ REDLITHIUM™  
HIGH OUTPUT™  
CP3.0 Battery Pack  
**48-11-1837**  
2-Pack

**NEW**



**48-11-1820**  
M18™ REDLITHIUM™  
CP2.0 Battery Pack



**48-11-1815**  
M18™ REDLITHIUM™  
CP1.5 Battery Pack



## M12™

**PORTABLE PRODUCTIVITY  
TRADE FOCUSED  
SYSTEM WIDE**



### FITS M12™ TOOLS



**MORE POWER AND RUN-TIME**



**48-11-2460**  
M12™ REDLITHIUM™  
XC6.0 Battery Pack



**48-11-2402**  
M12™ REDLITHIUM™  
XC3.0 Battery Pack  
**48-11-2412**  
2-Pack



**LESS WEIGHT AND SMALLER SIZE**



**48-11-2430**  
M12™ REDLITHIUM™  
CP3.0 Battery Pack



**48-11-2420**  
M12™ REDLITHIUM™  
CP2.0 Battery Pack



**48-11-2401**  
M12™ REDLITHIUM™  
CP1.5 Battery Pack  
**48-11-2411**  
2-Pack



# SUPER, RAPID & STANDARD CHARGING SOLUTIONS

CHARGE UP TO

# 4X FASTER

with **SUPERCHARGER**

**REDLITHIUM™**  
HIGH OUTPUT HD12.0



**1 HR SUPER\***

**2 HR RAPID**

**4 HR STANDARD**

CHARGE TIME

	SUPER			RAPID			STANDARD					
<b>CHARGES UP TO 4X FASTER</b>												
<b>FEATURES</b>	M18™ and M12™ Super Charger 48-59-1811	M18™ and M12™ Rapid Charger 48-59-1808	M18™ and M12™ Rapid Charge Station 48-59-1807	M18™ and M12™ Multi-Voltage Charger 48-59-1812	M18™ and M12™ Vehicle Charger 48-59-1810	M18™ Six Pack Sequential Charger 48-59-1806	M12™ Charger 48-59-2401	M12™ Compact Charger and Power Source 48-59-1201	M12™ Four Bay Sequential Charger 48-59-1204	M18™ ROCKET™ Tower Light/Charger 2135	M18™ RADIUS™ Site Light/Charger w/ ONE-KEY™ 2150	M18™ Jobsite Radio/Charger 2792
M18™ Ports	1	1	3	1	1	6				1	2	1
M12™ Ports	1	1	3	1	1		1	1	4			
Charge Type	Sequential	Sequential	3 Packs Simultaneous	Sequential	Sequential	Sequential	Single	Single	Sequential	Single	Sequential	Single
Power Source	AC	AC	AC	AC	DC	AC	AC	AC or USB	AC	AC	AC	AC
Carry Handle			✓			✓				✓	✓	✓
Wall Mountable	✓	✓	✓	✓	✓	✓	✓		✓			

Optimized for **HIGH OUTPUT™** Batteries

**SUPERCHARGER**

**RAPIDCHARGER**

**STANDARD CHARGER**

	HIGH OUTPUT™									
	M18™ HD12.0	M18™ XC8.0	M18™ XC6.0	M18™ CP3.0	M18™ HD9.0	M18™ XC5.0	M18™ CP2.0	M12™ XC3.0	M12™ CP2.0	
<b>SUPERCHARGER</b>	60 min	45 min	35 min	35 min	103 min	70 min	27 min	46 min	30 min	
<b>RAPIDCHARGER</b>	130 min	83 min	65 min	35 min	103 min	60 min	27 min	46 min	30 min	
<b>STANDARD CHARGER</b>	241 min	162 min	123 min	65 min	184 min	105 min	42 min	63 min	43 min	

\*Estimated charge durations based on testing conducted by Milwaukee Tool at room temperature. Actual results may vary. Visit [milwaukeetool.com/charge](http://milwaukeetool.com/charge) for a comprehensive list of charge durations.



**REDLINK™ INTELLIGENCE**  
in Every MILWAUKEE® Charger

REDLINK™ Intelligence optimizes charge rates based on the battery type and temperature. This provides the best combination of charge time and pack life.