

TRIP ALARM SWITCH CHANGEOVER CONTACTS TYPE HQ
(7MM) ELECTRONIC ACCESSORY FOR 3VA4/5/6-BREAKER



Model	
Product brand name	SENTRON
Product designation	Tripped signaling switch
Design of the product	Accessories for 3VA circuit breakers
accessories	Tripped signaling switch
General technical data	
Degree of pollution	3
Overvoltage category	III
Voltage	
Tension assignée d'isolement U_i	690 V
Tension assignée de tenue aux chocs	4 kV
Operating voltage / at AC / acc. to CSA and UL	24 V
Operating voltage / at DC / acc. to CSA and UL	24 V
Rated operational voltage U_e at AC 50 Hz	24 V
Rated operational voltage U_e with DC	24 V
Electricity	
Thermal current	0.3 A
Operating current	

- at AC-12 / at 12 V
- at AC-12 / at 24 V
- at DC-12 / at 12 V
- at DC-12 / at 24 V
- at DC-13 / at 12 V
- at DC-13 / at 24 V
- at AC-15 / at 12 V
- at AC-15 / at 24 V

0.3 A
0.3 A
0.1 A
0.1 A
0.07 A
0.07 A
0.3 A
0.3 A

Mechanical Design

Width / Note	1 slot (7 mm)
Tightening torque / with screw-type terminals / minimum	0.4 N·m
Tightening torque / with screw-type terminals / maximum	0.5 N·m

Connections according IEC

Wire stripping length	15 mm
Connectable conductor cross-section	
• minimum	0.5 mm ²
• maximum	1.5 mm ²
AWG number / as coded connectable conductor cross section / for auxiliary contacts	
• minimum	20
• maximum	16

Connections according UL

Wire stripping length [in]	0.6 in
Tightening torque [lbf·in] / with screw-type terminals / minimum	3.5 lbf·in
Tightening torque [lbf·in] / with screw-type terminals / maximum	4.4 lbf·in

Certificates

General Product Approval	EMC	Declaration of Conformity	other
--------------------------	-----	---------------------------	-------



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9978-0AB13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9978-0AB13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9978-0AB13

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



2.

4.

TAS

1.

last modified:

11/17/2017