

**TBQC Cables**

Part Number	Description	Lifecycle Status
IC693CBL327	Cable, Left Side, One - 24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.	Mature
IC693CBL328	Cable, Right Side, One - 24 Pin 90 Degree Connector, 3 Meter. Cable has a connector on only one end and open on the other. Cable used with TBQC I/O Face Plate Adapter or Fujitsu style I/O modules.	Mature
IC693CBL329	Cable, Left Side, One - 24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Mature
IC693CBL330	Cable, Right Side, One - 24 Pin 90 Degree Connector, 1 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Mature
IC693CBL331	Cable, Left Side, One - 24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Mature
IC693CBL332	Cable, Right Side, One - 24 Pin 90 Degree Connector, 2 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Mature
IC693CBL333	Cable, Left Side, One - 24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Mature
IC693CBL334	Cable, Right Side, One - 24 Pin 90 Degree Connector, 0.5 Meter. from TBQC I/O Face Plate Adapter to TBQC Interposing Terminal Block.	Mature

**High Density Terminal Block Quick Connect**

The High Density TBQC is simple to use — just attach the connector terminal block to the I/O module, snap the remote terminal base on the DIN-rail and attach the cable. Installation is accomplished in seconds versus up to an hour of cutting, stripping and wiring 36 individual wires. The High Density TBQC is compatible with IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported.

**HDTBQC I/O Module Face Plate Adapter**

Part Number	Description	Lifecycle Status
IC694TBC032	High-density, 36-point, terminal block with cable connector. IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported.	Mature

**HDTBQC Interposing Terminal Block**

Part Number	Description	Lifecycle Status
IC694RTB032	High-density remote base, 36-point, with shield ground lug and removable terminal blocks. IC695ALGxxx, IC69xMDL660 and IC694MDL664 modules only. Discrete output modules not supported.	Mature

**HDTBQC Interface Cables**

Part Number	Description	Lifecycle Status
IC694CBL005	Shielded 0.5 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.	Mature
IC694CBL010	Shielded 1.0 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.	Mature
IC694CBL030	Shielded 3.0 meter cable with termination on both ends. IC694TBC032 and IC694RTB032 only.	Mature
IC694CBL130	Shielded 3.0 meter cable with termination on one end that connects to the IC694TBC032 terminal block. The other end of the cable is non-terminated wires.	Mature

**External Power Supplies**

Part Number	Description	Lifecycle Status
IC690PWR024	Field Power Supply 24 VDC 5 Amps	Mature
IC690PWR124	Field Power Supply 24 VDC 10 Amps	Mature

**Rack to Rack Expansion Cables**

Part Number	Description	Lifecycle Status
IC693CBL300	Cable, I/O Base Expansion, 1 Meter, Shielded	Mature
IC693CBL301	Cable, I/O Base Expansion, 2 Meters, Shielded	Mature
IC693CBL302	Cable, I/O Base Expansion, 15 Meters, Shielded with built-in terminator	Mature
IC693CBL312	Cable, I/O Base Expansion, 0.15 Meter, Shielded	Mature
IC693CBL313	Cable, I/O Base Expansion, 8 Meters, Shielded	Mature
IC693ACC307	I/O Bus Terminator Plug	Mature