

available.

300mm

LED Undercabinet Light Ultra Slim



installation. If using a plug-in power supply, a separate dimmer controller is

Installation and ordering information on reverse.


¹ Available separately.

LED Undercabinet Light RA Ultra Slim



INSTALLATION DIAGRAM


POWER SUPPLY REQUIREMENT



Cable Connector

LIGHT PATTERN

| | | | | | * IMPORTANT * |
|------------|----------|---|----------|---|------------------|
| | | | | | |
| UC-LED1000 | | х | 11 Watts | = | |
| UC-LED-500 | | х | 5 Watts | = | |
| UC-LED-300 | | х | 3 Watts | = | |
| PRODUCT | # PIECES | | WATTAGE | | TOTAL WATTAGE |



RDERING INFO \cap

| PRODUCT | PROD# | DESCRIPTION | WATT | DIMENSIONS | | | |
|----------------------------------|----------------------------------|--|-------------------------|--|--|--|--|
| Natural White Unit * 4000K | 88861 88862 88863 | UC-LED300-NW UC-LED500-NW UC-LED1000-NW | 3W 5W 11W | L-300mm L-500mm L-1000mm | | | |
| Warm White Unit * 3000K | 88875 88876 88877 | UC-LED300-WW UC-LED500-WW UC-LED1000-WW | 3W 5W 11W | L-300mm L-500mm L-1000mm | | | |
| Plug-in Power Supply | 88864 88865 88866 88867 | UC-6W Power Supply UC-12W Power Supply UC-24W Power Supply UC-36W Power Supply | 6W 12W 24W 36W | L-45mm x W-25mm x D-31mm L-68mm x W-25mm x D-50mm L-96mm x W-30mm x D-45mm L-96mm x W-30mm x D-45mm | | | |
| Hardwire Power Supply | 89097 89098 89099 | UC/A LED DRIVER 40W 24VDC DIM UC/A LED DRIVER 60W 24VDC DIM UC/A LED DRIVER 96W 24VDC DIM | 40W 60W 96W | | | | |
| Dimmer (for plug-in power supply |) 88872 | UC-Dimmer Controller | | L-85mm x W-25.4mm x D-12.7mm | | | |
| On/Off Switch | 88871 | UC-Switch Connector | | L-33mm x W-33mm x D-8mm | | | |
| Output Receptacle (splitter) | 88873 88874 | UC RCPT DC 4 (Allows you to split the low voltage power into 4 separate runs) UC RCPT DC 8 (Allows you to split the low voltage power into 8 separate runs) | | | | | |
| Cable Connector | 88868 | UC-Connector Cable | | L-1m Cord | | | |
| Corner Connector | 88869 | UC-Corner Connector 90° | | W-45mm | | | |

MUST NOT EXCEED 36WATTS

* EACH UNIT INCLUDES: (1) fixture, (1) direct connector, (1) cable connector, (2) mounting plates and (2) screws

² For use with multiple run applications. Output receptacle (splitter) is required to tie in runs to 100W or 150W transformer



Visit rabdesign.ca to view our entire collection.

RAB Design Lighting Inc. 222 Islington Ave., Toronto, ON M8V 3W7 TEL. 416-252-9454 / 800-268-0381 | FAX. 416-252-9664 / 800-668-5517

