


Alternate Catalog No. VEM4 Catalog No. 1SBN030111R1000

Description: VEM4 Mechanical and Electrical Interlock Unit

UPC No 3471523130616

Home > Contactors > UL Listed IEC Contactors > AF Contactors

Mechanical and electrical interlock sets VEM4 mechanical and electrical interlock set for the interlocking of two AF contactors. VEM4 set includes a mechanical interlock unit VM4 with 2 fixing clips (BB4) and a VE4 electrical interlock block with A2-A2 connection. Fixing the electrical interlock block to the contactor front face connects the 2 built-in N.C. interlocking contacts with the two coils. VE4 block must be used with A2-A2 connection to respect the electrical connection diagram.



Representative Image

Descriptors

Category	AF Contactors
Block Contactor Type	Accessory

Specifications

Product Type	AF
Terminal Type	Screw Terminals
Number of Auxiliary Contacts NO	1
RoHS Status	Following EU Directive 2011/65/EU
Number of Auxiliary Contacts NC	1
Tightening Torque UL/CSA	Auxiliary Circuit 11 IA
Conventional Free-air Thermal Current	acc. to IEC 60947-5-1, q = 40 °C 16 A
Maximum Electrical Switching Frequency	1200 _B7HUR cycles per hour
Rated Insulation Voltage	acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Maximum Mechanical Switching Frequency	1800 cycles per hour
Secondary Rated Impulse Withstand Voltage	6 kV
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 m ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5/2x 0.75 ... 1.5 m ² Rigid 1/2x 1 ... 2.5 m ²
Wire Stripping Length	Auxiliary Circuit 10 mm

Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 6.0	EC001044 - Mechanic interlock for switch
ETIM 7	EC001044 - Mechanic interlock for switch
ETIM 5.0	EC002498 - Accessories for low-voltage switch technology

Dimensions

Product Net Weight	0.035 kg
--------------------	----------

Package Information

Package Level 1 Width	92 mm
Package Level 1 Depth / Length	35 mm
Package Level 1 EAN	3471523130616
Package Level 1 Units	box 1 piece
Package Level 2 Units	132 piece
Package Level 3 Units	3168 piece
Package Level 2 Gross Weight	4.62 kg

Ordering

Minimum Order Quantity	1
------------------------	---