

Communications

For industry-leading tools for datacom, telecom and fiber optic applications, Greenlee has the complete product line. Choose from a large line-up of premium installation tools, tone generators and telecommunication test sets, network certification instruments and fiber optic test equipment – produced and field-tested to perform from start to finish.

Contents

Hand Tools	234
Fiber Optic Tools	276
Identification	281
Testing	291
Fiber Optic Testing	308
Locators	334
Kits	338
Fiber Optic Kits	354



MADE FOR THE TRADE!™



HAND TOOLS

PowerPlay Multi-Tool Family	PT-540	PT-525	PT-510
110 Punchdown Tool	•	•	•
66 Punchdown Tool	•	•	
UTP Round Wire Stripper	•	•	
Extra Large Wire Cutter (up to 10 AWG Romex [®])	•		
Large Wire Cutter (up to 12 AWG Romex [®])		•	
Wire Cutter (up to Cat5e UTP cable)		•	•
Hard Wire Cutter Notch	•	•	•
18/20/22/24 AWG Wire Strippers	•	•	•
10 AWG Wire Stripper	•		
12 AWG Wire Stripper	•	•	
14 AWG Wire Stripper	•		
Needle Nose & Gripping Pliers	•	•	•
Drywall Punch	•	•	•
Drywall Saw	•	•	
24-18 AWG Lug Terminal Crimpers	•		
18-14 AWG Lug Terminal Crimpers	•		
Wire Hook & Spudger	•	•	
¼" Socket Drive & Hex Bit Adapter	•	•	
#4 & #6 Slotted Screwdrivers	•	•	•
#1 Phillips Screwdriver	•	•	•
SOG Serrated Knife	•	•	•
3-in-1 File & Bottle Opener	•	•	•
7/16" & 3/8" Nut Drivers	•		
Ruler & Lanyard	•	•	•
Pivoting Handle Covers	•	•	
PowerLocks [™]	•	•	

PowerPlay[™] PT-540



30 Tools-In-One:

- Needle Nose and Gripping Pliers.
- 110 and 66 Punchdown Tools.
- UTP and Round Wire Stripper.
- Extra Large Wire Cutter – up to 10 AWG Romex[®].
- Wire Cutter – up to Cat5e UTP cable.
- 7 Wire Strippers - 10/12/14/18/20/22/24 AWG.
- PowerLocks[™] Secure Folding Components.
- Drywall Punch and Saw.
- Hard Wire Cutter Notch.
- 24-18 AWG Lug Terminal Crimpers.
- 18-14 AWG Lug Terminal Crimpers.
- Wire Hook and Spudger.
- #4 and #6 Slotted Screwdrivers.
- #1 Phillips Screwdriver.
- SOG Knife with ½ Serrated BladeA.
- 3-in-1 File and Bottle Opener.
- 7/16" and 3/8" Nut Drivers.
- Ruler and Lanyard.
- Leather Sheath Included.

CAT. NO.	DESCRIPTION
PA6520	PowerPlay [™] PT-540

SPECIFICATIONS

Length	
Closed	5" (127 mm)
Open	7.5" (191 mm)
Weight	10.4 oz. (295 g)

PA4945 PowerPlay Grip Pack Kit

Contains the tools you need to install or maintain data and voice patch panels and outlets. See page 338 for details.

PowerPlay™ PT-525



24 Tools-In-One:

- Needle Nose & Gripping Pliers.
- 110 & 66 Punchdown Tools.
- Romex® Wire Cutter.
- UTP Stripper.
- 6 Wire Strippers - 12/14/18/20/22/24 AWG.
- Drywall Punch & Saw.
- #4 & #6 Slotted Screwdrivers.
- #1 Phillips Screwdriver.
- 1/4" Square Drive with Hex Bit Adapter.
- SOG Serrated Knife.
- 3-in-1 File.
- Wire Hook & Spudger.
- Bottle Opener.
- Ruler.
- Leather Sheath included.

CAT. NO.	DESCRIPTION
PA6510	PowerPlay™ PT-525

SPECIFICATIONS

Length	
Closed	4.75" (121 mm)
Open	7" (178 mm)
Weight	9.6 oz. (272 g)

PowerPlay™ PT-510



18 Tools-In-One:

- Needle Nose & Gripping Pliers.
- 110 Punchdown Tool.
- Romex® Wire Cutter.
- #4 & #6 Slotted Screwdrivers.
- #1 Phillips Screwdriver.
- SOG Serrated Knife.
- Drywall Punch.
- 4 Wire Strippers - 18/20/22/24 AWG.
- 3-in-1 File.
- Bottle Opener.
- Ruler.
- Leather Sheath included.

CAT. NO.	DESCRIPTION
PA6500	PowerPlay™ PT-510

SPECIFICATIONS

Length	
Closed	4.25" (114 mm)
Open	6" (152 mm)
Weight	7.5 oz. (227 g)

CAT. NO.	DESCRIPTION
PA6501	R 110 Punchdown Blade with 18/20/22/24 AWG Strippers
PA6502	R 66 Punchdown Blade with 18/20/22/24 AWG Strippers
PA6503	R Wire Hook and Spudger
PA6504	R SOG Knife with 1/2 Serrated Blade
PA6505	R Drywall Saw
PA6506	R 3-in-1 File/#6 Slotted Screwdriver
PA6507	R Scissors
PA6508	R #1 Phillips Screwdriver
PA6509	R Replacement Handle Cover (1)

CAT. NO.	DESCRIPTION
PA6511	R #4 Slotted Screwdriver/Bottle Opener
PA6512	R 1/4" Drive
PA6524	R StopLock™
PA6514	R Telephone Unwrap Bit
PA6515	R Telephone Wrap Bit
PA6516	R 1/4" Socket Adapter
PA6518	R PT-510 Leather Sheath
PA6519	R PT-525/PT-540 Leather Sheath