




Fuseless starters

	Description	For use with contactor	ac/dc	Frame size	Cat. no.	Ref. no.	Pack.					
Link modules 	For mechanical and electrical connection between contactors and manual motor starters	MC0.., MC1..	ac/dc	GPS1	GPF1LMCBA	101410	5					
		CL00A..., CL01A..., CL02A..	ac	GPS1	GPF1L02AA	101411	5					
		CL00D..., CL01D..., CL02D..	dc	GPS1	GPF1L02DA	101412	5					
		CL25A..	ac	GPS1	GPF1L25AA	101413	5					
		CL25D..	dc	GPS1	GPF1L25DA	101414	5					
		CL03A..., CL04A..	ac	GPS1	GPF1L04AA	107165	5					
		CL03D..., CL04D..	dc	GPS1	GPF1L04DA	107166	5					
		CL03A..., CL04A..	ac	GPS2	GPF2L04AA	107190	5					
		CL45A..	ac	GPS2	GPF2L45AA	101415	5					
		CL03D..., CL04D..	dc	GPS2	GPF2L04DA	107191	5					
		CL45D..	dc	GPS2	GPF2L45DA	101416	5					
		CL06A..., CL07A..	ac	GPS2	GPF2L07AA	101417	5					
		Record Plus with CL09/10A										
		For mechanical and electrical connection between contactor and thermal overload relays RT1	CL00.. - CL25	ac/dc	GPS1	GPF1L25CT1	101512	5				
	CL03.. - CL45	ac/dc	GPS2	GPF1L45CT1	101513	5						
Base plates 	Plastic plates for mounting the fuseless starter in panels or in 35 mm DIN rail	CL00.., CL01.., CL02.., CL25..	ac/dc	GPS1	GPF1B1A	101418	5					
		CL03.., CL04.. and CL45..	ac/dc	GPS2	GPF2B2A	101419	5					
		CL06.., CL07..	ac/dc	GPS2	GPF2B3A	101420	5					
		CL03.., CL04..	ac/dc	GP	GPF1B4A	107163	5					
Base plates Link connector	For use with MCCB Record Plus	-	-	-	GPF3B5A	107253	1					
	For two base plates for reversing applications	-	-	-	GPF1CBA	101427	10					
Plastic cover 	Description	For use with contactor			Cat. no.	Ref. no.	Pack.					
								Fit the plastic cover into the front of the correspondent contactor to allow a clear identification of the terminal numbering	CL00.., CL01.. and CL02 without built-in auxiliary contact	GPF00C02	107098	5
									CL00.., CL01.. and CL02 with built-in 1NO auxiliary contact	GPF10C02	107099	5
									CL00.., CL01.. and CL02 with built-in 1NC auxiliary contact	GPF01C02	107100	5
									CL25..	GPF00C25	107101	2
									CL03.., CL04.. without built-in auxiliary contact	GPF00C04	107102	5
									CL03.., CL04.. with built-in 1NO auxiliary contact	GPF10C04	107103	5
									CL03.., CL04.. with built-in 1NC auxiliary contact	GPF01C04	107105	5
									CL45..	GPF00C45	107106	5
									CL06.., CL07..	GPF00C08	107107	5

Order codes

Intro

A

B

C

D

E

F

G

H

I

J/X

