

Push-buttons

Standard / Momentary



Description	Cat. no.	Ref. no. see bottom	Cat. no.	Ref. no. see bottom	Cat. no.	Ref. no. see bottom
	Metal		Plastic		Plastic	
With flush cap	P9MPN●G		P9XPN●G		P9SPN●G	
With raised cap	P9MPN●S		P9XPN●S		P9SPN●S	
Recessed	P9MPN●E					

Mushroom head / Momentary



Mushroom head Ø 28 mm	P9MEM3●N		P9XEM3●N			
Mushroom head Ø 40 mm	P9MEM4●N		P9XEM4●N			
Mushroom head Ø 60 mm	P9MEM6●N		P9XEM6●N			
Mushroom head ∇ 30 mm					P9SEM3●N	

Mushroom head / Emergency with latch

Standard



Push-pull to release

Mushroom head Ø40 mm	P9MET4●N1		P9XET4●N1		P9SET4●N1	
----------------------	------------------	--	------------------	--	------------------	--

Push-twist to release

Red mushroom head Ø28 mm	P9MER3RN	184070	P9XER3RN	185070		
Red mushroom head Ø40 mm	P9MER4RN	184071	P9XER4RN	185071		

Push-key to release

Red mushroom head Ø40 mm	P9MEC4RN▲		P9XEC4RN▲			
--------------------------	------------------	--	------------------	--	--	--

Positive break in accordance with EN 418



Push-twist to release

Red mushroom head Ø40 mm			P9XER4RA	185072	P9SER4RA	186072
--------------------------	--	--	-----------------	--------	-----------------	--------

Push-key to release

Red mushroom head Ø40 mm			P9XEC4RA▲		P9SEC4RA▲	
--------------------------	--	--	------------------	--	------------------	--

Mushroom head / 3 positions



Ø40 mm 1-0 fixed. 2 transient	P9MET4●N2		P9XET4●N2		P9SET4●N2	
Ø40 mm 0 fixed. 1-2 transient	P9MET4●N3		P9XET4●N3		P9SET4●N3	

With keylock ⁽¹⁾

Key withdrawable in position I & II



normal	P9MPCN1K▲		P9XPCN1K▲			
depressed	P9MPCN2K▲		P9XPCN2K▲			
normal & depressed	P9MPCN3K▲		P9XPCN3K▲			

Key withdrawable position III



Lockable position



normal	P9MPCN1E▲		P9XPCN1E▲			
depressed	P9MPCN2E▲		P9XPCN2E▲			
normal & depressed	P9MPCN3E▲		P9XPCN3E▲			

(1) Keys on E.16

The catalogue numbers in **bold** are available from stock.

Colours		black	red	green	yellow	brown	bleu	white	grey	without cap
Caps	●	N	R	V	G	M	L	B	H	0
Mushroom heads	●	N	R	V	G	-	L	-	-	-

Remark: To complete the catalogue number, substitute the symbol ● by a letter for the choice of the colour and the symbol ▲ by a number for the type of the key.

For reference numbers, see chapter X, pg. X.10



Selector switches with knob

2 positions



Fixed

With spring return

Function (1)	Cat. no.	Ref. no. see bottom	Cat. no.	Ref. no. see bottom	Cat. no.	Ref. no. see bottom			
							Metal	Plastic	Plastic
	P9MSMD0		P9XSMD0		P9SSMD0				
	P9MSMI0		P9XSMI0		P9SSMI0				
	P9MSMH0		P9XSMH0		P9SSMH0				
	P9MSMD5		P9XSMD5		P9SSMD5				
	P9MSMI5		P9XSMI5		P9SSMI5				
	P9MSMH1		P9XSMH1		P9SSMH1				

3 positions



Fixed

With spring return

	E	P9MSME0		P9XSME0		P9SSME0
	L	P9MSML0		P9XSML0		P9SSML0
	U	P9MSMU0		P9XSMU0		P9SSMU0
	Z, B	P9MSMZ0		P9XSMZ0		P9SSMZ0
	E	P9MSME1		P9XSME1		P9SSME1
	L	P9MSML1		P9XSML1		P9SSML1
	U	P9MSMU1		P9XSMU1		P9SSMU1
	Z, B	P9MSMZ1		P9XSMZ1		P9SSMZ1
	E	P9MSME5		P9XSME5		P9SSME5
	L	P9MSML5		P9XSML5		P9SSML5
	U	P9MSMU5		P9XSMU5		P9SSMU5
	Z, B	P9MSMZ5		P9XSMZ5		P9SSMZ5
	E	P9MSME3		P9XSME3		P9SSME3
	L	P9MSML3		P9XSML3		P9SSML3
	U	P9MSMU3		P9XSMU3		P9SSMU3
	Z, B	P9MSMZ3		P9XSMZ3		P9SSMZ3

4 positions

Fixed

With spring return

	X	P9MSMX0		P9XSMX0		P9SSMX0
	X	P9MSMX5		P9XSMX5		P9SSMX5

5 positions

Fixed

	X	P9MSMY0		P9XSMY0		P9SSMY0
	W	P9MSMW0		P9XSMW0		P9SSMW0

(1) Electrical diagrams, see E.24

The catalogue numbers in **bold** are available from stock.

Colours		black	red	green	yellow	bleu
Caps	●	N	R	V	G	L

For reference numbers, see chapter X, pg. X.10