

# Molded Case Circuit Breakers


## Q-Line Circuit Breakers

Cable-in Cable-out (lug-lug)  
240V Class

## Section 6

### TQD 240 Vac, Internal Common Trip

# of Poles	Ampere Rating	240 Vac Interrupting Rating	Product Number <sup>1,2</sup>
2	100	10kA	TQD22100WL
2	125	10kA	TQD22125WL
2	150	10kA	TQD22150WL
2	175	10kA	TQD22175WL
2	200	10kA	TQD22200WL
2	225	10kA	TQD22225WL
3	100	10kA	TQD32100WL
3	125	10kA	TQD32125WL
3	150	10kA	TQD32150WL
3	175	10kA	TQD32175WL
3	200	10kA	TQD32200WL
3	225	10kA	TQD32225WL



TJD432400WL

### TQD 240 Vac, Internal Common Trip with Factory Installed 120 Vac Shunt Trip<sup>3</sup>

# of Poles	Ampere Rating	240 Vac Interrupting Rating	Product Number <sup>1,2</sup>
3	125	10kA	TQD32125ST1
3	150	10kA	TQD32150ST1
3	175	10kA	TQD32175ST1
3	200	10kA	TQD32200ST1
3	225	10kA	TQD32225ST1

### THQD 240 Vac, Internal Common Trip

# of Poles	Ampere Rating	240 Vac Interrupting Rating	Product Number <sup>1,2</sup>
2	100	22kA	THQD22100WL
2	125	22kA	THQD22125WL
2	150	22kA	THQD22150WL
2	175	22kA	THQD22175WL
2	200	22kA	THQD22200WL
2	225	22kA	THQD22225WL
3	100	22kA	THQD32100WL
3	125	22kA	THQD32125WL
3	150	22kA	THQD32150WL
3	175	22kA	THQD32175WL
3	200	22kA	THQD32200WL
3	225	22kA	THQD32225WL

### TJD 240 Vac, Internal Common Trip

# of Poles	Ampere Rating	240 Vac Interrupting Rating	Product Number <sup>1,2</sup>
2	250	22kA	TJD422250WL
2	300	22kA	TJD422300WL
2	350	22kA	TJD422350WL
2	400	22kA	TJD422400WL
2	400 Molded Case Switch	22kA	TJD422Y400
3	250	22kA	TJD432250WL <sup>4</sup>
3	300	22kA	TJD432300WL <sup>4</sup>
3	350	22kA	TJD432350WL <sup>4</sup>
3	400	22kA	TJD432400WL <sup>4</sup>
3	400 Molded Case Switch	22kA	TJD432Y400 <sup>4</sup>

<sup>1</sup>Refer to table on page 6-103 for lug and wire range data.

<sup>2</sup>Includes line and load lugs. For optional configurations see page 6-3.

<sup>3</sup>For additional shunt trip options see page 6-41.

<sup>4</sup>TJD uses same accessories as J600 line. TJD not listed HACR.

UL listed HACR (heating, air conditioning and refrigeration).

