

# RACK SCREWS

## NEW Premium Rack Screws


**NEW** Premium rack screws provide the best bit engagement in the industry. HG hardware features salt spray resistant plating that slows rust build-up and is ideal for marine and high-humidity installations. HM hardware features an attractive black matte finish. Both types are truss-head hardware, 10-32 threaded, 3/4" long with pre-installed washers and self-guiding pilot points.



Part #	Qty	Finish
HG	100 pc.	salt spray resistant, black gloss
HG500	500 pc. in a reusable jar	salt spray resistant, black gloss
HM	100 pc.	black matte
HM500	500 pc. in a reusable jar	black matte




**NEW** HG hardware is recommended for use in humid and marine applications



## Standard Rack Screws

Standard 3/4" long rack screws with 10-32 threads feature self-guiding pilot points. HP Series truss head screws provide a clean, modern appearance and fit under optional trim strips (see pg. 120) for the most attractive finish. HW Series trim-head screws feature an older, classic appearance. Includes factory-installed nylon washer.

Black Part #	Silver Part #	Head	Qty
HP500	-	truss-head	500 pc. in a reusable jar
HP	CHP	truss-head	100 pc.
HPS	-	truss-head	25 pc.
HW500	-	trim-head	500 pc. in a reusable jar
HW100	-	trim-head	100 pc.




## Security Rack Screws

Security screws are the ideal way to keep people from tampering with rackmounted equipment. The highest security patented Guardian Series™ hardware is unique to Middle Atlantic Products and features a square post drive that cannot be found elsewhere. All screws are 10-32 by 3/4" and include factory-installed black nylon washer and black finish.

Rack Screw Part #	Qty	Bit Part #	Description
HSK	100 pc. screws	SPBIT	<b>Highest Security</b> patented square post drive bit to drive HSK Guardian Series™ security screws
HTX	50 pc. screws	TBIT	star post bit to drive HTX security screws
HS	100 pc. screws	SBIT	square drive bit to drive HS security screws

**HSK Guardian Series™** security hardware



## Cable Friendly Short Rack Screws

Cable friendly HPQ Series screws are 5/8" long with 10-32 threads and feature a rounded end to allow wires to be dressed inside front rackrail without chafing. Featuring an attractive Phillips truss head, finished in black.

Part #	Quantity
HPQ-500	500 pc. in a reusable jar
HPQ	100 pc.



## Cage Nut Hardware

Cage nuts fit our WRK, MRK, and DRK cage-nut style rackrail and are available to fit 10-32 and 6mm rack screws to accommodate slide out servers.

Part #	Description
CN1032-50	50 pc. 10-32 cage nuts
CN6MM-100	100 pc. 6MM cage nuts

## 12-24 and 6MM Rack Screws

Primarily used in telecommunications and data, these 5/8" long 12-24 and 6MM threaded screws are heat-treated to prevent head stripping. Finished in black, includes nylon washers.

Part #	Qty
HP-24	100 pc. 12-24 thread
HP24-500	500 pc. 12-24 thread in a reusable jar
HP-6MM	100 pc. 6MM Phillips head rack screws



## Shoulder Washers

When used in conjunction with the pre-installed washers supplied on our screws, these black nylon shoulder washers will electrically isolate the equipment from the rackrails to help prevent ground loops. 100 piece count. NOTE: not for use with HPQ, HP-6MM and HP-24 screws

Part #	Qty
SW	100 pc.

