



BRAD NAILERS & STAPLERS	98-101
TACKERS	101
STAPLES & BRADS	102-105
GLUE GUNS	106-107
GLUE STICKS	107-108
RIVETERS	109
RIVETS & PLATES	110-111

STANLEY
®

CONSUMER FASTENING SELECTION GUIDES

STAPLERS		DURABILITY	EASY SQUEEZE	H/I/L POWER SETTING	STAPLES	BRADS	DESK STAPLES	FASTENER TYPE
Electric Staplers								
Electric Stapler / Brad Nailer TRE550	xxxxx	N/A		x	x	x		
Manual staplers								
Heavy-Duty Staple Gun / Brad Nailer TR250	xxxxx	xxxxx		x	x	x		
Heavy-Duty Staple Gun with Hi/Lo Setting TR150HL	xxxx	xxxxx		x	x			
Heavy-Duty Staple Gun TR150	xxx	xxxxx		x	x			
Heavy-Duty Staple Gun/ Cable Tacker CT10X	xxx	xxx		x	x			
All Steel Light-Duty Chrome-Plated Staple Gun TR45	xx	xxx			x			
All Plastic Light-Duty Staple Gun Kit TR45K	xx	xxx			x			
Electric Brad Nailer TRE650	xxxx	N/A		x			x	
Heavy-Duty Hammer Tacker PHT250C	xxxxx	N/A			x			
Hammer Tacker PHT150C	xxx	N/A			x			
Plier Stapler TR65	xxx	xxx					x	

GLUE	GR100	GR90C	GR25	GR20	GR15	GR10	
DUAL MELT STANDARD GLUE STICKS							
GS10DT					x		
GS15DT	x		x	x	x	x	
GS20DT	x		x	x	x	x	
GS25DT	x		x	x	x	x	
ALL-PURPOSE STANDARD CLEAR GLUE STICKS							
GS040					x	x	
GS230	x	x	x	x	x		
STANDARD WOODWORKING GLUE							
GS260	x	x	x	x	x	x	
FORMULA II SUPER STRENGTH STANDARD GLUE STICKS							
GS500	x	x	x	x	x	x	

RIVETS	SIZE	MR100CG	MR77C	MR55CS	MR33C
STEEL RIVETS					
PSS42	1/8" X 1/8"	x	x	x	x
PSS44	1/8" X 1/4"	x	x	x	x
PSS46	1/8" X 3/8"	x	x	x	x
PSS48	1/8" X 1/2"	x	x	x	x
STAINLESS-STEEL RIVETS					
PTT42	1/8" X 1/8"	x		x	x
PTT44	1/8" X 1/4"	x		x	
PTT48	1/8" X 1/2"	x		x	
PTT52	5/32" X 1/8"	x			
PTT54	5/32" X 1/4"	x		x	
PTT64	3/16" X 1/4"				
ALUMINUM RIVETS					
PAA42	1/8" X 1/8"	x	x	x	x
PAA42W	1/8" X 1/8" white	x	x	x	x
PAA44	1/8" X 1/4"	x	x	x	x
PAA46	1/8" X 3/8"	x	x	x	x
PAA48	1/8" X 1/2"	x	x	x	x
PAA52	5/32" X 1/8"	x	x	x	x
PAA54	5/32" X 1/4"	x	x	x	x
PAA58	5/32" X 1/2"	x	x	x	x
PAA610	3/16" X 5/8"	x	x	x	x
PAA62	3/16" X 1/8"	x	x	x	x
PAA64	3/16" X 1/4"	x	x	x	x
PAA66	3/16" X 3/8"	x	x	x	x
PAA68	3/16" X 1/2"	x	x	x	x
RIVET PACK					
R120	Assortment	x	x	x	x

RIVETERS / GLUE GUNS	DURABILITY	FEATURE
RIVETERS		
Contractor Grade Riveter MR100CG	xxxxx	Heavy-Duty
Swivel Head Riveter MR77C	xxxx	Swivel Head
Right-Angle Riveter MR55CS	xxx	Right Angled
Medium-Duty Riveter MR33C	xxx	Right Angled
GLUE GUNS		
DualMelt Pro™ Glue Gun Kit GR100	xxxxx	High & Low Settings
Trigger-Feed Dual-Melt Glue Gun GR25	xxx	High & Low Settings
Mini Dual-Temp Glue Gun GR15	xxx	High & Low Settings
Trigger Feed Hot-Melt Glue Gun GR20	xx	High Setting
Mini Hot-Melt Glue Gun GR10	xx	High Setting

STAPLES	SIZE	TR250	TR150HL	TR150	CT10X	TR45	TR45K	TRE650	PHT250C	PHT150C	TR65
HEAVY-DUTY STAPLES	MR77C										
TRA704T	1/4"	X	X	X	X				X	X	
TRA705vT	5/16"	X	X	X	X				X	X	X
TRA706T	3/8"	X	X	X	X				X	X	X
TRA708T	1/2"	X	X	X	X				X		
TRA709T	9/16"	X	X	X	X						
HEAVY-DUTY STAINLESS-STEEL NARROW CROWN STAPLES											
TRA704SST	1/4"	X	X	X	X				X	X	
TRA705SST	5/16"	X	X	X	X				X	X	X
TRA706SST	3/8"	X	X	X	X				X	X	X
TRA708SST	1/2"	X	X	X	X				X		
TRA709SST	9/16"	X	X	X	X						
HEAVY-DUTY MONEL NARROW CROWN STAPLES											
TRA704MT	1/4"	X	X	X	X				X	X	
TRA705MT	5/16"	X	X	X	X				X	X	X
TRA706MT	3/8"	X	X	X	X				X	X	X
TRA708MT	1/2"	X	X	X	X				X		
TRA709MT	9/16"	X	X	X	X						
LIGHT-DUTY STAPLES											
TRA204T	1/4"					X	X				
TRA205T	5/16"					X	X				
TRA206T	3/8"					X	X				
TRS105T	5/16"										
CABLE STAPLES											
CT106T	3/8"					X					
CT107T	7/16"					X					
CT108T	1/2"					X					
CT109T	9/16"					X					
STAPLES											
SWKBN050	1/2"	X	X								
SWKBN562	9/16"	X	X								
SWKBN625	5/8"	X	X						X		
SWKBN075	3/4"							X	X		
SWKBBN075	3/4"								X		
SWKBBN100	1"							X	X		
SWKWBN100	1"							X	X		
SWKBN1187	1-3/16"							X	X		
SWKBN1250	1-1/4"							X	X		
CABLE STAPLES											
SWKBN562	9/16"	X	X								
SWKBN625	5/8"	X	X						X		
SWKBN050	1/2"	X	X								
SWKBN562	9/16"	X	X								
SWKBN625	5/8"	X	X						X		
SWKBN050	1/2"	X	X								
SWKBN562	9/16"	X	X								
SWKBN625	5/8"	X	X							X	
HEAVY-DUTY FLAT NARROW CROWN STAPLES											
CT305T	5/16"										
CT306T	3/8"										
CT308T	1/2"										
POWERCROWN® STAPLES											
TR0400	Stnd. Office Staple										x
HEAVY-DUTY POWERCROWN® STAPLES											
TRB504T	1/4"										
TRB505T	5/16"										
TRB506T	3/8"										
TRB508T	1/2"										
TRB509T	9/16"										
HEAVY-DUTY WIDE CROWN STAPLES											
TRC604T	1/4"										
TRC605T	5/16"										
TRC606T	3/8"										
TRC608T	1/2"										
TRC609T	9/16"										

Stanley® CT10X and Arrow® T-25®

Bostitch® PowerCrown® Tools

Ace®, Black & Decker®, Craftsman® and Duo Fast Wide Crown® products