

D4/6.NOIR V2



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	D4/6.NOIR V2
Product ID:	1SNA105140R0200
EAN:	3472591051407
Catalog Description:	D4/6.Black V2 Screw Clamp Terminal Blocks
Long Description:	D4/6 Screw Clamp Terminal Blocks - Feed-through - Black,4mm ² RatedCrossSection, 6mm Spacing TH 35-7.5, TH 35-15 Rail.

Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-A screw clamp
Instructions and Manuals:	1SNC160001C0207-CH-A screw clamp

Dimensions

Product Net Width:	6 mm
Product Net Height:	44.5 mm
Product Net Depth / Length:	40.5 mm
Product Net Weight:	10 g

Technical

Connection Type:	Screw clamp
Number of Levels:	1
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225051U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220020E1002

Instructions and Manuals: 1SNC160001C0207-CH-A screw clamp

RMRS Certificate: 1SND161007A1101

Classifications

Object Classification Code: X

ETIM 4: EC000897 - Feed-through terminal block

ETIM 5: EC000897 - Feed-through terminal block

ETIM 6: EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 50 piece

Package Level 1 Width: 61 mm

Package Level 1 Depth / Length: 220 mm

Package Level 1 Height: 47 mm

Package Level 1 Gross Weight: 0.5 kg

Package Level 1 EAN: 3472591051407

Package Level 2 Units: 2000 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 500 mm

Package Level 2 Height: 300 mm

Package Level 3 Units: 48000 piece

Product Packing Type: Box

