

# 3M™ Air-Mate™ 2000 Self-Contained Breathing Apparatus (SCBA)

30 min.  
Supplied Air (Optional)

Maximum protection, maximum durability

The Air-Mate 2000 system is for workers who require respiratory protection for environments that are immediately dangerous to life and health (IDLH). It's NIOSH-approved for both entry into and escape from

confined spaces. Optional airline connection enables the wearer to remain in IDLH atmospheres for extended periods of time.

Easily viewable shoulder-mounted, low-pressure gauge indicates cylinder air pressure.

Audible end-of-service alarm alerts wearer of low air supply.



Full facepiece features quarter-turn pressure-demand valve for a secure attachment.

First-breath activation allows the unit to be donned in a non-hazardous environment before connecting the pressure-demand valve.

Built-in speaking diaphragm allows clear communication with co-workers.



Quick-release cylinder band clamp makes cylinder changes quick and easy.

Single-piston, first-stage, fail-open regulator has few moving parts, improving dependability and reducing maintenance costs.



Ergonomically designed backplate distributes weight evenly, providing maximum comfort.

## 3M Air-Mate 2000 SCBA Ordering Information

Part No.	Description	Cylinder Type	PSI	Rated Duration	Vest Harness Material
BA-2430-S	2000 (small facepiece)	Aluminum	2216	30 Min.	Cordura™ Nylon
BA-2530-S	2000 w/Airline (small facepiece)	Aluminum	2216	30 Min.	Cordura™ Nylon
BA-2430-M	2000 (medium facepiece)	Aluminum	2216	30 Min.	Cordura™ Nylon
BA-2530-M	2000 w/Airline (medium facepiece)	Aluminum	2216	30 Min.	Cordura™ Nylon
BA-2430-L	2000 (large facepiece)	Aluminum	2216	30 Min.	Cordura™ Nylon
BA-2530-L	2000 w/Airline (large facepiece)	Aluminum	2216	30 Min.	Cordura™ Nylon
BAP-2003933	Cylinder and Valve	Aluminum	2216	30 Min.	

# 3M™ Air-Mate™ SCBAG™ Self-Contained Breathing Apparatus (SCBA)

30 min.

Supplied Air (Optional)

## Nothing is more convenient

The SCBAG system is unlike any other product in its class. It's stored in a unique, reversible carrying bag that opens to form a vest with the SCBA system in place and ready to use. Portable and donned easily in a matter of seconds, it's perfect for confined spaces and emergency use,

and it makes training simple. It's NIOSH-approved for both entry into and escape from confined spaces. Optional airline connection enables wearer to remain in IDLH atmospheres for extended periods of time.

**Full facepiece features quarter-turn pressure-demand valve for a secure attachment.**

**First-breath activation allows the unit to be donned in a non-hazardous environment before connecting the pressure-demand valve.**

**Easily viewable shoulder-mounted, low-pressure gauge indicates cylinder air pressure. Audible end-of-service alarm alerts wearer of low air supply.**

**Lightweight, vest-style harness features improved shoulder and back padding and distributes weight evenly for greater comfort.**

**Adjusts up to 58" in chest size for improved fit.**

**Hook-and-loop harness closure adjustment provides fast and easy donning.**



Front pouch stores and protects the facepiece until needed.



Lightweight, hoop-wrapped, 30-minute cylinder is positioned for ideal weight distribution and easier valve access.



3M Air-Mate SCBAG SCBA is a bag that opens to form a vest with the SCBA system in place and ready to use. The SCBAG is available with a durable, black Cordura™ nylon harness or a flame-resistant brown Advance™ Harness.

## 3M Air-Mate SCBAG SCBA Ordering Information

Part No.	Description	Cylinder Type	PSI	Rated Duration	Vest Harness Material
BA-4430-S	SCBAG (small facepiece)	Hoop Wrapped	4500	30 Min.	Cordura™ Nylon
BA-4530-S	SCBAG w/Airline (small facepiece)	Hoop Wrapped	4500	30 Min.	Cordura™ Nylon
BA-4430-M	SCBAG (medium facepiece)	Hoop Wrapped	4500	30 Min.	Cordura™ Nylon
BA-4530-M	SCBAG w/Airline (medium facepiece)	Hoop Wrapped	4500	30 Min.	Cordura™ Nylon
BA-4430-L	SCBAG (large facepiece)	Hoop Wrapped	4500	30 Min.	Cordura™ Nylon
BA-4530-L	SCBAG w/Airline (large facepiece)	Hoop Wrapped	4500	30 Min.	Cordura™ Nylon
BA-4630-S	SCBAG (small facepiece)	Hoop Wrapped	4500	30 Min.	Advance™
BA-4730-S	SCBAG w/Airline (small facepiece)	Hoop Wrapped	4500	30 Min.	Advance™
BA-4630-M	SCBAG (medium facepiece)	Hoop Wrapped	4500	30 Min.	Advance™
BA-4730-M	SCBAG w/Airline (medium facepiece)	Hoop Wrapped	4500	30 Min.	Advance™
BA-4630-L	SCBAG (large facepiece)	Hoop Wrapped	4500	30 Min.	Advance™
BA-4730-L	SCBAG w/Airline (large facepiece)	Hoop Wrapped	4500	30 Min.	Advance™
BAP-2003930	Cylinder and Valve	Hoop Wrapped	4500	30 Min.	