


## Cable-to-Cable or Cable-to-Rod Connectors

**One-piece construction for cable-to-cable, cable-to-rod, “T” and “X” connections**

- Suitable for direct burial or in concrete
- Replaces exothermic welds
- Made from high-conductivity wrought copper



Cat. No.	Cable to Cable Range						Rod to Cable range						
	Main	Die Code	TBM14 and 15 Die Cat. No.	Branch	Die Code	TBM14 and 15 Die Cat. No.	Ground Rod (in.)	Die Code	TBM14 and 15 Die Cat. No.	Cable	Die Code	TBM14 and 15 Die Cat. No.	
GG21-21	#2 or #1	45	15526SS [2]	#2 or #1	45	15526SS [2]							
GG10-10	1/0	54	15511SS [2]	1/0	54	15511SS [2]							
GG2030-21	2/0 or 3/0	60	15532SS [2]	#2 or #1	50-45	15526SS [2] 15530SS	-	-	-	-	-	-	
GG2030-10				1/0	54H	15511SS [2]							
GG2030-2030				2/0-3/0	60	15532SS [2]							
GG40250-21	4/0 or 250 kcmil	71H	15514SS [2]	#2	45 50	15526SS [2] 15530SS	1/2 5/8	71 80H	15514SS 15517SS	#2 or #1 #2 or #1	45 50	15526SS 15530SS	
GG40250-10				1/0 kcmil	54H	15511SS [2]				1/0	54	15511SS	
GG40250-2030				2/0 or 3/0	60	15532SS [2]				2/0 or 3/0 2/0 or 3/0	60 60	15532SS 15532SS	
GG40250-40250				4/0 or 250 kcmil	71H	15514SS [2]				4/0 or 250 kcmil	71H	15514SS	
GG500-40250	500 kcmil	87H	15506SS [2]	4/0 or 250 kcmil	71H	15514SS [2]	3/4 5/8	87H	15506SS	4/0 or 250 4/0 or 250	71H 71H	15514SS 15514SS	
GG500-500				500 kcmil	87H	15506SS [2]				500	87H	15506SS	
GG500-350				350 kcmil	80H	15606SS [2]				350	80H	15606SS	
GG500-2030				2/0 or 3/0	60	15532SS [2]				2/0 or 3/0	60	15532SS	
GG350-350				350 kcmil	80H	15606SS [2]				350 kcmil	80H	15606SS [2]	-

Uses 15500TB adaptor for 15-Ton Tools.  
Optional ground rod knurling die or TBM14 and 15 tools: 15508SS.  
Optional ground rod knurling tool: 240-31565-94.

[\*] Number of crimps.