




Appliance & Wall Switch Timers



A,
B,
C



D

F

H

Heavy Duty Appliance Timers

A. HB112C Air Conditioner & Appliance Timer

- Automatically controls 240 volt air conditioners, heaters, heavy-duty appliances and lamps
- 3,750 watt capacity
- Plugs directly into wall outlet
- 2 ON/2 OFF settings per day
- 3-prong 220-240 Volt grounded plug and receptacle
- Manual override ON/OFF switch



3750W/240V/
2 H.P. 240V Max.
Motor Load

B. HB114C Air Conditioner & Appliance Timer

- Same as HB112C except for the following:
- 5,000 Watt capacity



5000W/240V/
2 H.P. 240V Max.
Motor Load

C. HB113C Air Conditioner & Appliance Timer

Same as HB112C except for the following:

- Automatically controls 120 Volt air conditioners, heaters, heavy-duty appliances and lamps
- 2,500 Watt capacity



2500W/120V/
1 H.P. 120V Max.
Motor Load

Wall Switch Timers

D. ST01C Heavy Duty In-Wall Timer with Astronomic Feature

Can be used with four separate programming options:
Same settings Monday through Friday, Saturday & Sunday,
all 7 days of the week or individual daily settings.

- DST for 2006, 2007 and flexible for future changes, if needed
- Set it once and never set it again; follows daily changes in sunrise/sunset times
- For single pole and three way applications up to 100 ft.
- Controls lighting including fluorescent and heavy duty loads such as fans and appliances
- Up to 6 ON/OFF settings per 7-day period a total of 42 ON/42 OFF settings per week
- Easy-to-set 6 button programming
- LCD digital clock and readout
- To-the-minute setting accuracy
- Battery backup
- Random setting feature available to avoid predictable "timer controlled" look
- Manual override feature
- Use with decorator-style wall plate (not included)
- Ratings:
 - Resistive: 15 A, 120-277 VAC
 - Tungsten: 15 A, 120 VAC, 6 A, 208-277 VAC
 - Ballast: 8 A, 120 VAC, 4 A, 208-277 VAC
 - Motor: 1 HP, 120 VAC, 2 HP, 240 VAC
 - DC Loads: 4 A, 12 VDS, 2 A, 28 VDS

F. EJ351C Programmable 24-hour Security Timer

- Up to 24 ON/24 OFF settings per day
- Random setting turns light ON and OFF at slightly different times each day
- Self-learning feature: if not manually programmed, it will repeat the first 24 hr. ON/OFF pattern
- 15 minute memory guard protects against power failure
- Replaces any standard wall light switch
- Use with existing wall plate; standard (toggle) or decorator (rocker) styles
- Ratings: 500 Watts Incandescent, 120 VAC, 60 Hz

G. EJ500C Indoor Digital Wall Switch Timer with Astronomic Feature

- Flushmount design
- 6 ON/6 OFF settings per day
- Controls incandescent and fluorescent (class "P" ballast) lighting
- Easy to set programming
- Set it once and never set it again; follows daily changes in sunrise/sunset times
- Battery backup guards against memory loss
- Replaces any standard wall switch
- Use with decorative style wall plate(not included)
- Ratings: 500 Watts Incandescent, 120 VAC, 60 Hz

E. ST01AC Heavy Duty In-Wall Timer with Astronomic Feature

Same as ST01C except Almond color

H. EJ500AC Indoor Digital Wall Switch Timer with Astronomic Feature

Same as EJ500C except Almond Color