

# Professional Grade Transformers

## Light Expressions™



Intermatic® professional grade transformers are the most reliable low voltage transformers available. Manufactured by Intermatic Incorporated – recognized worldwide for high quality timers and system controls – these transformers are especially designed for trouble-free operation and long lasting durability. Ensure that all of your professional lighting installations operate trouble-free and provide long-lasting service by using only Intermatic® professional grade transformers.

“Your success can depend on it!”

### Every professional grade transformer includes these important product features:

- Heavy gauge steel housings with rain-tight covers (Model AL60TW uses a high impact polymer construction)
- Complete ground shield protection for safe operation. Suitable for use with submersible luminaries or submersible pumps
- Suitable for use with submersible luminaries or submersible pumps
- Meets UL and cCSAus safety standards
- Automatic or resettable circuit breakers for overload protection, helps prevent damage to electrical components, caused by overheating

#### A. AL300TPWS

- Heavy-duty 16 ga. stainless steel case
- Built-in photo control option
- Manual ON/OFF switch
- Fully programmable timer
- One set of 300 watt terminal blocks
- Heavy-duty power cord
- 5 Year limited warranty
- Resettable circuit breaker
- Rain tight enclosure with lifetime limited warranty

#### B. AL600TPWS

- Heavy-duty 16 ga. stainless steel case
- Built-in photo control option
- Manual ON/OFF switch
- Fully programmable timer
- Two sets of 300 watt terminal blocks
- Heavy-duty power cord
- 5 year limited warranty
- Resettable circuit breaker
- Rain tight enclosure with lifetime limited warranty

#### C. AL900TPWS

- Heavy-duty 16 ga. stainless steel case
- Built-in photo control option
- Manual ON/OFF switch
- Fully programmable timer
- Three sets of 300 watt terminal blocks
- Heavy-duty power cord
- 5 year limited warranty
- Resettable circuit breaker
- Rain tight enclosure with lifetime limited warranty

#### D. AL300RTW

- Heavy-duty 18 ga. steel housing
- Manual ON/OFF switch
- Fully programmable timer
- One set of 300 watt terminal blocks
- Heavy-duty power cord
- 5 year limited warranty
- Automatic circuit breaker
- Rain tight enclosure

#### E. AL600TW

- Heavy-duty 18 ga. steel housing
- Manual ON/OFF switch
- Fully programmable timer
- Two sets of 300 watt terminal blocks
- Heavy-duty power cord
- 5 year limited warranty
- Automatic circuit breaker
- Rain tight enclosure

#### F. AL900TW

- Heavy-duty 18 ga. steel housing
- Manual ON/OFF switch
- Fully programmable timer
- Three sets of 300 watt terminal blocks
- Heavy-duty power cord
- 5 year limited warranty
- Automatic circuit breaker
- Rain tight enclosure



All Intermatic AL Transformers meet UL1838 Standards