

Weatherproof Metallic Covers

Single-Gang Device Covers



CCD



CCDV



CCG



CCGV

CAT. NO.	COLOR	DESCRIPTION
Duplex Receptacle Cover, Horizontal		
CCD	Silver	Device Mount
CCD-L	Silver	Device Mount with Lock Option
CCD-FS	Silver	Box Mount
WR81-CN	Natural	Cover, Stay-Open Lid
WRH80-C	Gray	Cover, Self-Closing Lids
D-PAK®		
DCCD-P	Silver	Non-Metallic Device Mount
DCCD	Silver	Device Mount
DCCD-BR	Bronze	Device Mount
DCCD-WH	White	Device Mount
DCCDSO	Silver	Device Mount, Stay Open
DCCDSO-BR	Bronze	Device Mount, Stay Open
DCCDSO-WH	White	Device Mount, Stay Open
Duplex Receptacle Cover, Vertical		
CCDV	Silver	Device Mount
CCDV-L	Silver	Device Mount with Lock Option
D-PAK®		
DCCDV	Silver	Device Mount
DCCDV-BR	Bronze	Device Mount
DCCDV-WH	White	Device Mount
GFCI Receptacle Cover, Horizontal		
CCG	Silver	Device Mount
CCG-FS	Silver	Box Mount
D-PAK®		
DCCG	Silver	Device Mount
DCCG-BR	Bronze	Device Mount
DCCG-WH	White	Device Mount
GFCI Receptacle Cover, Vertical		
CCGV	Silver	Device Mount
CCGV-L	Silver	Device Mount with Lock Option
D-PAK®		
DCCGV	Silver	Device Mount
DCCGV-BR	Bronze	Device Mount
DCCGV-WH	White	Device Mount



CCS



CCSV



CCSV-TL



CCMB



CCT-1


CAT. NO.	COLOR	DESCRIPTION
Single Receptacle Cover, Horizontal — 1.485" Diameter Opening		
CCS	Silver	Device Mount
Single Receptacle Cover, Vertical — 1.59"/2.156" Diameter Opening		
CCSV	Silver	Device Mount
CCSV-L	Silver	Device Mount with Lock Option
CCPO	Silver	Power Outlet Cover with 2.156" Diameter Opening, Box Mount
CCPO-L	Silver	Box Mount with Lock Option
Single Receptacle Cover, Vertical — 1.59" Opening		
CCSV-TL	Silver	Device Mount Integral Locking Hasp
Motor Base Plug and Cover, Horizontal		
CCMB	Silver	Device Mount 15A, 125V Motor Base Plug
Switch Cover Only		
CCT	Silver	Device Mount Switch Cover Only, Packed with Spacers and Screws
Switch Cover with Switch		
CCT-1	Silver	Single-Pole 15A, 125V
CCT-1-20	Silver	Single-Pole 20A, 120-277V
CCT-3	Silver	3-Way Switch 15A, 125V
Note: Raintight when used with appropriate Red•Dot® boxes.		
SW1	Silver	One-Gang Cover with 10A, 125V Single-Pole Switch
SW2	Silver	One-Gang Cover with 10A, 125V Double-Pole Switch
SW20-1/710	Silver	One-Gang Cover with 20A, 102/277V Single-Pole Switch (special oil- and gas-resistant gasket)
SW20-2	Silver	One-Gang Cover with 20A, 102/277V Double-Pole Switch
SW20-2/710	Silver	One-Gang Cover with 20A, 102/277V Double-Pole Switch (special oil- and gas-resistant gasket)

Note: All covers packed with gasket and screws.

UL Listed E-18407.

CSA Certified LR-18685.

Single-Gang Gaskets



CAT. NO.	COLOR	DESCRIPTION
CCK	Black	Neoprene
CCSK	Black	Neoprene