







# Turnlok® Devices

## Receptacles, Connectors & Plugs

3 Wire Grounded 15A, 250V & 277VAC

Pass & Seymour  
**legrand**

Turnlok® Devices

Catalog Number	Rating A. V.	Description/ Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					 UL498	 FSUL WC596	 CSA
<b>Receptacles</b>							
4560	15 250	Single Receptacle		L6-15R	•		
+4550	15 250	Duplex Receptacle		L6-15R	•		
4760	15 277*	Single Receptacle		L7-15R	•		•
4750	15 277*	Duplex Receptacle		L7-15R	•		•
<b>Connectors IP20 Suitability</b>							
L615-C	15 250	Black Shell, Yellow Face	.230"-.690"	L6-15R	•	•	•
 L615-CCN	15 250	Black Shell, Yellow Face	.230"-.690"	L6-15R	•	•	•
L715-C	15 277*	Black Shell, Yellow Face	.230"-.690"	L7-15R	•	•	•
<b>Plugs IP20 Suitability</b>							
L615-P	15 250	Black Shell, Yellow Face	.230"-.690"	L6-15P	•	•	•
 L615-PCN	15 250	Black Shell, Yellow Face	.230"-.690"	L6-15P	•	•	•
L715-P	15 277*	Black Shell, Yellow Face	.230"-.690"	L7-15P	•	•	•
 Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.							

\* Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.


\*AC only. +Not designed for split currents

Catalog Number	Description
<b>Accessories</b>	
L15-RBC	Weatherproof Boot, Connector
L15-RBP	Weatherproof Boot, Plug
3720-FS	*Weatherproof Cover—4560/4760
WP7	*Weatherproof Cover—4560/4760
3710-FS	*Weatherproof Cover—4550/4750
WP8	*Weatherproof Cover—4550/4750
S7	Stainless Steel Plate—4560/4760
S8	Stainless Steel Plate—4550/4750
FC22-GL	+EHU-Strain Relief Grip
FC30-GL	+EHU-Strain Relief Grip
FC40-GL	+EHU-Strain Relief Grip
FC52-GL	+EHU-Strain Relief Grip
PSLD	Lockout Device


\*For further information consult the Weatherproof Section R.

+For further information consult the Flexcor® Section K.


2-Pole 3-Wire




All devices listed on this page conform to NEMA WD-1.




4550




4560




4760



4750



15A Plug










15A Connector






Receptacles, Connectors & Plugs

# Turnlok® Devices

## Receptacles, Connectors, Plugs, Inlet, Outlet

3 Wire Grounded 15A, 125V



Catalog Number	Rating A. V.	Description/ Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					 UL498	FSUL WC596	 CSA
<b>Receptacles</b>							
4710	15 125	Single Receptacle		L5-15R	•		•
4700	15 125	Duplex Receptacle		L5-15R	•		•
4792	15 125	Combination Straight Blade and Locking		5-15R & L5-15R	•		
<b>Connectors IP20 Suitability</b>							
L515-C	15 125	Black Shell, Yellow Face	.230"-.690"	L5-15R	•	•	•
 L515-CCN	15 125	Black Shell, Yellow Face	.230"-.690"	L5-15R	•	•	•
CRL515-C	15 125	Corrosion Resistant	.230"-.690"	L5-15R	•	•	•
<b>Plugs IP20 Suitability</b>							
L515-P	15 125	Black Shell, Yellow Face	.230"-.690"	L5-15P	•	•	•
 L515-PCN	15 125	Black Shell, Yellow Face	.230"-.690"	L5-15P	•	•	•
CRL515-P	15 125	Corrosion Resistant	.230"-.690"	L5-15P	•	•	•
4720-SSAN	15 125	Angle	.230"-.625"	L5-15P	•		•
<b>Flanged Inlet &amp; Outlet</b>							
4716-SS	15 125	Flanged Inlet		L5-15P	•		•
4715-SS	15 125	Flanged Outlet		L5-15R	•		•
 Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.							

2-Pole 3-Wire

All devices listed on this page conform to NEMA WD-1.

NEMA  
L5-15RNEMA  
L5-15PNEMA  
5-15R

Catalog Number	Description	Catalog Number	Description
<b>Accessories</b>			
L15-RBC	Weatherproof Boot, Connector	S7	Stainless Steel Plate—4710
L15-RBP	Weatherproof Boot, Plug	S8	Stainless Steel Plate—4700/CR4700/4792
3720-FS	*Weatherproof Cover—4710	FC22-GL	+EHU-Strain Relief Grip
WP7	*Weatherproof Cover—4710	FC30-GL	+EHU-Strain Relief Grip
3710-FS	*Weatherproof Cover—4700	FC40-GL	+EHU-Strain Relief Grip
WP8	*Weatherproof Cover—4700	FC52-GL	+EHU-Strain Relief Grip
WPG1	*Weatherproof Cover for Flanged Inlet and Outlet	PSLD	Lockout Device

\*For further information consult the Weatherproof Section R.

+For further information consult the Flexcor® Section K.