

Logic Control General Purpose Relays

Section 10

CR420

Plug-In Relays
DPDT, 10A, 240 VAC
3PDT, 10A, 240 VAC
DPDT, 5A, 240 VAC
4PDT, 5A, 240 VAC

CR420K

No. of Poles	Contacts	Contact Rating	Mounting type	Indicating Options	Product Number	GO-10PR
2	DPDT	10A	Socket	Push to test & LED	CR420KPC022*	
2	DPDT	10A	Socket	Push to Test	CR420KPM022*	
3	3PDT	10A	Socket	Push to test & LED	CR420KPC033*	
3	3PDT	10A	Socket	Push to Test	CR420KPM033*	

Specify a complete product number by including coil suffix in place of *, see Coil Suffix Table below for coil codes.
Please consult factory, if desired product configuration does not appear.



Coil Suffix Table

AC	6V	12V	24V	120V	240V
	A	B	C	J	N
DC	12V	24V	48V	110V	125V
	2	4	7	9	5

Accessories

Description	Product Number
Socket for Panel/DIN Rail Mount (DPDT)	CR420KA2
Socket for Panel/DIN Rail Mount (3PDT)	CR420KA3
Socket for Panel/DIN Rail Mount (DPDT)	CR420KA21
Socket for Panel/DIN Rail Mount (3PDT)	CR420KA31
Hold-down Clips ²	CR420KAS

Contact factory regarding versions not shown here.

²Quantity is 2 per product number; order 1 CR420KAS per socket. Quantity and selection based on socket, not on relay.

CR420M

No. of Poles	Contacts	Contact Rating	Mounting type	Indicating Options	Product Number	GO-10PR
2	DPDT	5A	Socket	None	CR420MPA022*	
2	DPDT	5A	Socket	Push to test & LED	CR420MPC022*	
2	DPDT	5A	Socket	LED Indicator	CR420MPL022*	
4	4PDT	5A	Socket	None	CR420MPA044*	
4	4PDT	5A	Socket	Push to test & LED	CR420MPC044*	
4	4PDT	5A	Socket	LED Indicator	CR420MPL044*	
4	4PDT	5A ¹	Socket	LED Indicator	CR420MPLG44*	

Specify a complete product number by including coil suffix in place of *, see Coil Suffix Table below for coil codes.
Please consult factory, if desired product configuration does not appear.

¹Au diffused contact suitable for low level switching.



Coil Suffix Table

AC	6V	12V	24V	120V	240V
	A	B	C	J	N
DC	12V	24V	48V	110V	125V
	2	4	7	9	5

Accessories

Description	Product Number
Socket for Panel/DIN Rail Mount	CR420MA
Hold-down Clips ²	CR420MAS

Contact factory regarding versions not shown here.

²Quantity is 2 per product number; order 1 CR420MAS per socket. Quantity and selection based on socket, not on relay.



Logic Control General Purpose Relays

Section 10

CR420

Plug-In Relays

SPDT, 15A, 240 VAC

DPDT, 10A, 240 VAC

4PDT, 10A, 240 VAC

CR420N

No. of Poles	Contacts	Contact Rating	Mounting type	Indicating Options	Product Number	GO-10PR
1	SPDT	15A	Socket	None	CR420NPA011*	
1	SPDT	10A	Socket	Push to test & LED	CR420NPC011*	
1	SPDT	10A	Socket	LED Indicator	CR420NPL011*	
1	SPDT	15A	Top Flange	None	CR420NTA011*	
2	DPDT	10A	Socket	None	CR420NPA022*	
2	DPDT	10A	Socket	Push to test & LED	CR420NPC022*	
2	DPDT	15A	Socket	LED Indicator	CR420NPL022*	
2	DPDT	10A	Top Flange	None	CR420NTA022*	
4	4PDT	10A	Socket	None	CR420NPA044*	
4	4PDT	10A	Socket	Push to test & LED	CR420NPC044*	
4	4PDT	10A	Socket	LED Indicator	CR420NPL044*	
4	4PDT	10A	Top Flange	None	CR420NTA044*	

Specify a complete product number by including coil suffix in place of *, see Coil Suffix Table below for coil codes.
Please consult factory, if desired product configuration does not appear.



Coil Suffix Table

AC	6V	12V	24V	120V	240V
	A	B	C	J	N
DC	12V	24V	48V	110V	125V
	2	4	7	9	5

Accessories

Description	Product Number
Socket for Panel/DIN Rail Mount	CR420NA2
Socket for Panel/DIN Rail Mount	CR420NA4
Socket for Panel/DIN Rail Mount	CR420NA21
Hold-down Clip ¹	CR420NAS
Hold-down Clips ²	CR420MAS

Contact factory regarding versions not shown here.

¹Fits CR420NA2 and NA21 sockets only. Quantity is 1 per product number; order 1 per socket. Quantity and selection is based on socket, not on relay.

²Fits CR420NA4 socket. Quantity is 2 per product number; order 1 CR420MAS per socket. Quantity and selection is based on socket, not on relay.



Product Number Selection Instructions: See page 10-2