



2-IN-1 IMPACT SOCKETS

- Two coaxial spring-loaded sockets in one tool
- Sockets have high-torque, 6 and 12-point designs making it easier to position on fasteners
- Deep socket with a 1/2" drive works great for pole hardware installation and removal
- Cross hole design helps maintain socket connection to adapter or impact wrench
- Sockets are color coded to quickly identify sizes
- Single-ended impact socket wrenches with hands free adjustment between socket sizes
- Engineered for use with impact wrenches including Klein's 1/2" Compact Impact Wrench (Cat. Nos. BAT20-CW/BAT20-CW1)
- Available individually or in convenient kits
- Sets include a case for storage



| Cat. No. | UPC 0-92644+ | Socket Sizes | 12-Point Sets | | | 6-Point Set |
|----------|-----------------|--------------------------------|------------------|------------------|-------------------|------------------|
| | | | 66010 65052-9 | 66040 38209-3 | 66050E 65075-8 | 66060 65088-8 |
| 66001 | 65046-8 | 3/4" & 9/16" | ● | ● | | |
| 66011 | 65053-6 | 1/2" & 3/8" | ● | ● | | |
| 66012 | 38206-2 | 5/8" & 7/16" | ● | ● | | |
| 66014 | 38207-9 | 7/8" & 11/16" | ● | ● | | |
| 66015 | 38208-6 | 1" & 13/16" | ● | | | |
| 66016 | 65054-3 | 1-1/8" & 15/16" | ● | | | |
| 66041 | 38211-6 | 1/4" Hex x 1/2" Square Adapter | | ● | ● | |
| 66051E | 65112-0 | 17 x 13 mm | | | ● | |
| 66052E | 65077-2 | 24 x 19 mm | | | ● | |
| 66053E | 65078-9 | 30 x 22 mm | | | ● | |
| 66054E | 65079-6 | 32 x 27 mm | | | ● | |
| 66004 | 38005-1 | 3/4" & 9/16" | | | | ● |
| 66061 | 65091-8 | 1/2" & 3/8" | | | | ● |
| 66062 | 65107-6 | 5/8" & 7/16" | | | | ● |
| 66064 | 65108-3 | 7/8" & 11/16" | | | | ● |
| 66065 | 65109-0 | 1" & 13/16" | | | | ● |
| 66066 | 65110-6 | 1-1/8" & 15/16" | | | | ● |



3-IN-1 & 4-IN-1 IMPACT SOCKETS

- Easily switch between sizes without removing your gloves
- Each tool includes multiple square socket sizes plus a 7/16" hex quick-change adapter
- Two coaxial spring-loaded sockets in one tool (Cat. No. NRHD4)
- Works on 1/2", 5/8" and 3/4" pole hardware
- 13/16" diameter, 6" (152 mm) long hollow shaft for use on long threaded bolts



NRHDA



NRHDA3




NRHDA4

NRHD4



NRHD3



NRHD

| Cat. No. | UPC 0-92644+ | Description | Socket Size | Overall Length |
|----------|--------------|-----------------------------|---------------------------|------------------|
| NRHD | 68021-2 | 3-in-1 Impact Socket | 3/4", 1", 1-1/8" | 7.75" (19.7 cm) |
| NRHD3 | 68643-6 | Single-Ended Impact Socket | 3/4", 1" & 1-1/8" | 10" (25.4 cm) |
| NRHD4 | 65049-9 | 4-in-1 Square Impact Socket | 3/4", 13/16", 1" & 1-1/8" | 9" (22.9 cm) |
| NRHDA | 68026-7 | Adapter for NRHD | 7/16" | 4.906" (12.5 cm) |
| NRHDA3 | 68062-5 | Adapter for NRHD3 | 1/2" | 2.469" (6.3 cm) |
| NRHDA4 | 65051-2 | Adapter for NRHD4 | 1/2" Male Square | 2.75" (7 cm) |



2-IN-1 COATED IMPACT SOCKET

- 20% lighter than traditional impact sockets*
- Blue coating is easy to spot in a crowded tool bag
- Engineered for use with impact tools including Klein's Compact Impact Wrench and Drill (Cat. Nos. BAT20CW, BAT20CW1, BAT20CD and BAT20CD1)
- Durable plastic coating protects against damage due to scratching and abrasion


*As compared to Klein Tools 66001 socket

3-IN-1 SLOTTED IMPACT SOCKET

- Features an alignment slot to tighten and loosen most hot-line clamps
- Patent pending design
- Engineered for use with impact tools including Klein's Compact Impact Wrench and Drill (Cat. Nos. BAT20CW, BAT20CW1, BAT20CD and BAT20CD1)
- Color coded with double lines to identify size and slotted feature



66030



66031

| Cat. No. | UPC 0-92644+ | Description | Socket Sizes | Points |
|----------|--------------|------------------------------|--------------|--------|
| 66030 | 65076-5 | 2-in-1 Coated Impact Socket | 3/4" & 9/16" | 12 |
| 66031 | 65087-1 | 3-in-1 Slotted Impact Socket | | |

⚠ Visit www.kleintools.com for warnings and instructions.



See our complete line of **Impact Sockets**
www.kleintools.com



© 2021 Klein Tools, Inc.
 Lincolnshire, IL 60069
 82965 Rev. 12/21 A