

Pilot and Signaling Devices Heavy-Duty 30.5 mm Watertight/Oiltight Accessories

Section 9

CR104P

Accessories, Components and Kits

600 Volts max. AC/DC

10 Amperes Continuous

Selector Switch Knobs

Depth (max. projection front of panel)	Color	Illumination	Product Number
1.16" (29.5 mm)	Black	Non-Illuminated	CR104PXM02B
1.16" (29.5 mm)	Red	Non-Illuminated	CR104PXM02R
1.16" (29.5 mm)	Yellow	Non-Illuminated	CR104PXM02E
1.16" (29.5 mm)	Green	Non-Illuminated	CR104PXM02G
1.16" (29.5 mm)	Blue	Non-Illuminated	CR104PXM02L
1.11" (28.2 mm)	Red	Illuminated	CR104PXL03R
1.11" (28.2 mm)	Yellow	Illuminated	CR104PXL03E
1.11" (28.2 mm)	Green	Illuminated	CR104PXL03G
1.11" (28.2 mm)	Blue	Illuminated	CR104PXL03L
1.11" (28.2 mm)	Amber	Illuminated	CR104PXL03M
1.11" (28.2 mm)	White	Illuminated	CR104PXL03W
1.11" (28.2 mm)	Clear	Illuminated	CR104PXL03C

Lenses

Depth (max. projection front of panel)	Color	Illumination	For use with	Product Number
1.20" (30.5 mm)	Red	Illuminated	Push Buttons	CR104PXL05R
1.20" (30.5 mm)	Yellow	Illuminated	Push Buttons	CR104PXL05E
1.20" (30.5 mm)	Green	Illuminated	Push Buttons	CR104PXL05G
1.20" (30.5 mm)	Blue	Illuminated	Push Buttons	CR104PXL05L
1.20" (30.5 mm)	Amber	Illuminated	Push Buttons	CR104PXL05M
1.20" (30.5 mm)	White	Illuminated	Push Buttons	CR104PXL05W
1.20" (30.5 mm)	Clear	Illuminated	Push Buttons	CR104PXL05C
0.92" (23.4 mm)	Red		Standard Pilot Lights	CR104PXL01R
0.92" (23.4 mm)	Yellow		Standard Pilot Lights	CR104PXL01E
0.92" (23.4 mm)	Green		Standard Pilot Lights	CR104PXL01G
0.92" (23.4 mm)	Blue		Standard Pilot Lights	CR104PXL01L
0.92" (23.4 mm)	Amber		Standard Pilot Lights	CR104PXL01M
0.92" (23.4 mm)	White		Standard Pilot Lights	CR104PXL01W
0.92" (23.4 mm)	Clear		Standard Pilot Lights	CR104PXL01C
1.20" (30.5 mm)	Red		Push-to-test Pilot Lights	CR104PXL07R
1.20" (30.5 mm)	Yellow		Push-to-test Pilot Lights	CR104PXL07E
1.20" (30.5 mm)	Green		Push-to-test Pilot Lights	CR104PXL07G
1.20" (30.5 mm)	Blue		Push-to-test Pilot Lights	CR104PXL07L
1.20" (30.5 mm)	Amber		Push-to-test Pilot Lights	CR104PXL07M
1.20" (30.5 mm)	White		Push-to-test Pilot Lights	CR104PXL07W
1.20" (30.5 mm)	Clear		Push-to-test Pilot Lights	CR104PXL07C

Lens and Divider

Color	For use with	Product Number
White	Cluster Type Pilot Lights	CR104PXL02W
White	Cluster Type Pilot Lights	CR104PXL04W



CR104PXM02* Non-Illuminated Knob



CR104PXL03* Illuminated Knob



CR104PXL05* Push Button Lens



CR104PXL01* Standard Pilot Light Lens



CR104PXL07* Push-to-Test Pilot Light Lens



CR104XL02* Cluster Type Lens and Divider

