

Using the Ampere, Frame, and kAIC Rating, Select the Appropriate Circuit Breaker

- For Spectra RMS, Include (1) rating plug per circuit breaker; For all other breaker types, no rating plug is required.
- If Lugs are included in the listed circuit breaker catalog number, "Included" will be listed in the *Terminal Lug* column. If lugs are required to be purchased separately, the most common (typical) lug catalog number will be listed. 3-Pole circuit breakers require (3) lugs; 2-Pole circuit breakers require (2) lugs

Using the Required Mounting Configuration, Select the Appropriate Bolt-on Mounting Kit

- The Mounting Kit Poles must be equal to or greater than the circuit breaker poles
 - 1- Pole CB = 2 or 3 Pole Mounting Kit
 - 2- Pole CB = 2 or 3 Pole Mounting Kit
 - 3-Pole CB = 3 Pole Mounting Kit
- Mounting Kits and filler plates should be ordered separately
- Fillers for unused spaces may also be ordered separately (p. 16)

Ampere Rating & Rating Plug Catalog #	CB Catalog Numbers by kAIC					Lug Catalog # (If not included in CB cat #)	Mounting Kit by # of Poles & Single or Dual Mounting		

Spectra G-Frame, 2-Pole

Spectra G-Frame, 2-Pole		UL 489 IC rating @ 480V		Terminal Lug	Spectra Bolt-On Mounting Kit				
AMPERE RATING	RATING PLUG	FRAME AMPS	65KA / 240V ONLY	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
125	SRPG400A125	400	SGDA22AT0400	SGHA26AT0400	SGLA26AT0400	SGPA26AT0400	TCLK265 (Order 1 kit)	Dual Mounted Mounting Kit - AMBC6GB Filler Plate - AFP4SGD Single Mounted Mounting Kit - AMCB3GM Filler Plate - AFP4SGS	Dual Mounted Mounting Kit - AMCB4GB Filler Plate - AFP4GSGD Single Mounted Mounting Kit - AMCB2GM Filler Plate - AFP4SGS
150	SRPG400A150								
175	SRPG400A175								
200	SRPG400A200								
225	SRPG400A225								
250	SRPG400A250								
300	SRPG400A300								
350	SRPG400A350								
400	SRPG400A400								
250	SRPG600A250	600		SGHA26AT0600	SGLA26AT0600	SGPA26AT0600	TCLK265 (Order 1 kit)		
300	SRPG600A300								
350	SRPG600A350								
400	SRPG600A400								
450	SRPG600A450								
500	SRPG600A500								
600	SRPG600A600								

Spectra RMS

Spectra E-Frame, 2-Pole

Spectra L Frame, 2 Pole			UL 489 IC rating @ 480V			Terminal Lug	Spectra Bolt-On Mounting Kit		
AMPERE RATING	RATING PLUG	FRAME AMPS	18KA	25KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
15	SRPE30A15	30	SEDA24AT0030	SEHA24AT0030	SELA24AT0030	SEPA24AT0030	TCAL18 (Order 2)	Dual Mounted Mounting Kit - AMCB6EB Filler Plate - AFP3SED	Dual Mounted Mounting Kit - AMCB4SE Filler Plate - AFP3SED
20	SRPE30A20								
25	SRPE30A25								
30	SRPE30A30								
35	SRPE60A35	60	SEDA24AT0060	SEHA24AT0060	SELA24AT0060	SEPA24AT0060		Single Mounted N/A - N/A	Single Mounted N/A - N/A
40	SRPE60A40								
45	SRPE60A45								
50	SRPE60A50								
60	SRPE60A60	100	SEDA24AT0100	SEHA24AT0100	SELA24AT0100	SEPA24AT0100			
70	SRPE100A70								
80	SRPE100A80								
90	SRPE100A90								
100	SRPE100A100	150	SEDA24AT0150	SEHA24AT0150	SELA24AT0150	SEPA24AT0150			
110	SRPE150A110								
125	SRPE150A125								
150	SRPE150A150								

Spectra E-Frame, 3-Pole

Spectra L-F Frame, 3-Pole			UL 489 IC rating @ 480V		Terminal Lug	Spectra Bolt-On Mounting Kit			
AMPERE RATING	RATING PLUG	FRAME AMPS	18KA	25KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
15	SRPE30A15	30	SEDA36AT0030	SEHA36AT0030	SELA36AT0030	SEPA36AT0030	TCAL18 (Order 3)	Dual Mounted Mounting Kit - AMCB6EB Filler Plate - AFP3SED	N/A
20	SRPE30A20								
25	SRPE30A25								
30	SRPE30A30								
35	SRPE60A35	60	SEDA36AT0060	SEHA36AT0060	SELA36AT0060	SEPA36AT0060		Single Mounted N/A - N/A	
40	SRPE60A40								
45	SRPE60A45								
50	SRPE60A50								
60	SRPE60A60	100	SEDA36AT0100	SEHA36AT0100	SELA36AT0100	SEPA36AT0100			
70	SRPE100A70								
80	SRPE100A80								
90	SRPE100A90								
100	SRPE100A100	150	SEDA36AT0150	SEHA36AT0150	SELA36AT0150	SEPA36AT0150			
110	SRPE150A110								
125	SRPE150A125								
150	SRPE150A150								

Spectra RMS (Cont.)

Spectra F-Frame, 2-Pole

UL 489 IC rating @ 480V						Terminal Lug	Spectra Bolt-On Mounting Kit	
AMPERE RATING	RATING PLUG	FRAME AMPS	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
70	SRPF250A70	250	SFHA24AT0250	SFLA24AT0250	SFPA24AT0250	TCAL29 (Order 2)	Dual Mounted Mounting Kit - AMCB6FJ Filler Plate - AFP3SFD Single Mounted Mounting Kit - AMCB3FJ Filler Plate - AFP3SFS	Dual Mounted Mounting Kit - AMCB4FJ Filler Plate - AFP3SFD Single Mounted Mounting Kit - AMCB2FJ Filler Plate - AFP3SFS
80	SRPF250A80							
90	SRPF250A90							
100	SRPF250A100							
110	SRPF250A110							
125	SRPF250A125							
150	SRPF250A150							
175	SRPF250A175							
200	SRPF250A200							
225	SRPF250A225							
250	SRPF250A250							

Spectra F-Frame, 3-Pole

UL 489 IC rating @ 480V						Terminal Lug	Spectra Bolt-On Mounting Kit	
AMPERE RATING	RATING PLUG	FRAME AMPS	35KA	65KA	100KA	TYPICAL	3-POLE	2-POLE
70	SRPF250A70	250	SFHA36AT0250	SFLA36AT0250	SFPA36AT0250	TCAL 29 (Order 3)	Dual Mounted Mounting Kit - AMCB6FJ Filler Plate - AFP3SFD Single Mounted Mounting Kit - AMCB3FJ Filler Plate - AFP3SFS	N/A
80	SRPF250A80							
90	SRPF250A90							
100	SRPF250A100							
110	SRPF250A110							
125	SRPF250A125							
150	SRPF250A150							
175	SRPF250A175							
200	SRPF250A200							
225	SRPF250A225							
250	SRPF250A250							