

# Juno<sup>®</sup> Wafer<sup>™</sup> LED Downlight Series

Switchable White Canless Recessed Downlight





### Juno<sup>®</sup> Wafer<sup>™</sup> LED Ultra-Thin and Installs Virtually Anywhere

Wafer LED Downlights with Switchable White features a switch for easy color temperature adjustment – while eliminating the need for recessed housings. Their innovative slim design allows for easy, remodel or new construction installation from below the ceiling.

Downlights are available in 4" and 6" aperture sizes, 90CRI+, 120V, and triac dimming down to 10%. They are wet location listed, making them ideal for use in a breadth of indoor and outdoor residential, hospitality, light commercial and multifamily applications.








## Fast, Easy, Housing-Free Installation

Ultra-Thin Wafer redefines recessed downlighting installations. With the slim design and remote driver box, Wafer can be installed in confined spaces such as closets, bathrooms, hallways, stairwells and outside soffits. These and other areas with shallow plenum space often make it impossible to install traditional recessed housings.

### Make installation quick and simple with the Wafer LED series.



### **Just 4 Simple Steps**





## Wafer<sup>™</sup> LED Downlight Trim Styles

With an IC rated design, Wafer LED provides either a flat smooth or regressed baffle trim style option to enhance the aesthetics of any application. For enhanced glare control, the Regressed Baffle provides a ½" regression which reduces glare and shadows at the ceiling plane. The crisp baffle lines softens the light output delivering comfortable light in the space.

### **Flat Smooth Trim**



**Matte White** 4" - 670 Lumens 6" - 970 Lumens



**Matte Black** 4" - 620 Lumens 6" - 900 Lumens

### **Regressed Baffle Low Glare Trim**



Matte White 4" - 650 Lumens 6" - 920 Lumens

## **Glare Control Made Simple**



#### **Regressed Frame**

The regressed lens provides less distracting glare, making the light source and Wafer less visible when viewing from a distance.

#### Wafer Regressed, Low Glare Baffle Trim Design


Ideal for Task Lighting – Used in areas with high productivity such as kitchens, bathrooms, and offices.

#### **Crisp Baffle Design**

Narrows the focus of the downlighting beam to trap and shape light to minimize glare

#### Wafer Flat, Smooth Trim Design

Ideal for General Lighting – Used in areas to feel safe and comfortable such as living rooms, basements, and hallways.




## Wafer<sup>™</sup> LED Switchable White Flexibility at your fingertips

The innovative Switchable White feature incorporates a switch for 5CCT color temperature adjustments. Too warm or too cool? Simply toggle the integrated switch to your desired setting and you are done! Whatever your application, Wafer with Switchable White are sure to give you the feel and flexibility that you need.



#### **5CCT Options**

Flexibility to switch color temperature to **2700/3000/ 3500/4000/5000K** CCT during installation to customize any application



111



### **Ordering Information**

WFEXC20 SW3PIN FT4

3-Pin 20FT Cable




Ultra-Thin Wafers Ordering Example: WF6 SWW5 90CRI MV								
Trim Series	Trim Style		Color Temperature		Rendering Index		Finish	
WF4 4" Wafer LED Downlight   WF6 6" Wafer LED Downlight	(blank) REG	Flat Smooth Regressed Baffle	SWW5	Switchable White (2700K, 3000K, 3500K, 4000K, 5000K)	90 CRI	90+ CRI	MW MB <sup>1</sup>	Matte White Matte Black Black only available in Flat.
A.S. Com		01		the second	•	-		alle .
78643 UNIVERSAL PAN DEDICATED PAN w Construction Pan 4" & 6" New Construction		Dan	WFJB Remodel Joist Bar			WFEXCx Switchable White Extension Cable		
			i r aii	nomodel 30	St Dui			Switchable white Extension cable
Accessories Order as separa	te catalog numb			nemouel so				Switchable white Extension cable
Accessories Order as separa Series 4-inch	ie catalog numt		Παιι	6-inch				Switchable white Extension cable
Series							Universal	New Construction Pan
Series 4-inch	Universa	per	1	<mark>6-inch</mark> WF8643 PAI	NU			
Series <mark>4-inch</mark> WF8643 PAN U	Universa	per al New Construction Pan Construction Pan, Reta	1	<mark>6-inch</mark> WF8643 PAI	N U 12			New Construction Pan Construction Pan, Retail Pack of 12
Series 4-inch WF8643 PAN U WF4 PAN R12	Universa 4" New 4" Goof	per al New Construction Pan Construction Pan, Reta	1	<mark>6-inch</mark> WF8643 PAI WF6 PAN R1	N U 12		6" New C	New Construction Pan Construction Pan, Retail Pack of 12 Ring
Series 4-inch WF8643 PAN U WF4 PAN R12 WF4GR MW JZ	Universa 4" New 4" Goof	per al New Construction Pan Construction Pan, Reta Ring I Joist Bar	1	<mark>6-inch</mark> WF8643 PAI WF6 PAN R1 WF6GR MW	N U 12 JZ		6" New C 6" Goof F	New Construction Pan Construction Pan, Retail Pack of 12 Ring Joist Bar

WFEXC20 SW3PIN FT4

Juno<sup>®</sup> Wafer<sup>™</sup> LED Recessed Downlights 7

3-Pin 20FT Cable





One Lithonia Way, Conyers, GA 30012 | Phone: 800.705.7378 | www.acuitybrands.com © 2020 Acuity Brands Lighting, Inc. All Rights Reserved. | JUN\_577666.01\_1020

