


RIGID PVC CONDUIT FITTINGS

ISSUE DATE:
DATE D'EMISSION: 2009 04 30

8X8 JUNCTION BOXES

SUPERCEDES:
REPLACE: 2004 08 15

1



PRODUCT CODE	PART NUMBER	NOMINAL SIZE		A		B		C	
		(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
076693	J887 STAHLIN	8	200	8.100	206	8.625	219	7.965	202
076692	J884 STAHLIN	8	200	8.075	205	8.625	219	7.965	202
076264	AMJB884 ALLIED	8	200	8.075	205	8.625	219	7.965	202
077671	JB 887	8	200	8.100	206	8.625	219	7.965	202
077664	JB 884	8	200	8.075	205	8.625	219	7.965	202
077678	JB 884 MEGATECH	8	200	8.075	205	8.625	219	7.965	202

PRODUCT CODE	PART NUMBER	NOMINAL SIZE		D		E		G	
		(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
076693	J887 STAHLIN	8	200	7.250	184	7.035	179	3.980	101
076692	J884 STAHLIN	8	200	4.230	107	4.005	102	3.980	101
076264	AMJB884 ALLIED	8	200	4.230	107	4.005	102	3.980	101
077671	JB 887	8	200	7.250	184	7.035	179	3.980	101
077664	JB 884	8	200	4.230	107	4.005	102	3.980	101
077678	JB 884 MEGATECH	8	200	4.230	107	4.005	102	3.980	101

PRODUCT CODE	PART NUMBER	NOMINAL SIZE		GASKET CODE	INSERT CODE	SCREW CODE	VOLUME	
		(in)	(mm)				(cu. in)	(cu. cm)
076693	J887 STAHLIN	8	200	097736	072549 (8)	072513 (4) 072515 (4)	434.0	7117.6
076692	J884 STAHLIN	8	200	097736	072549 (8)	072513 (4) 072515 (4)	248.0	4067.2
076264	AMJB884 ALLIED	8	200	097736	072549 (8)	072513 (4) 072515 (4)	248.0	4067.2
077671	JB 887	8	200	097736	072549 (8)	072513 (4) 072515 (4)	434.0	7117.6
077664	JB 884	8	200	097736	072549 (8)	072513 (4) 072515 (4)	248.0	4067.2
077678	JB 884 MEGATECH	8	200	072048	072549 (8)	072513 (4) 072515 (4)	248.0	4067.2

COMES WITH LARGE MOUNTING FEET, 097740

COVER DIMENSIONS

