

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Test Sockets

## General Information

<b>Extended Product Type:</b>	AL2
<b>Product ID:</b>	1SNA163043R2100
<b>EAN:</b>	3472591630435
<b>Catalog Description:</b>	AL2-H12-M3 Test Sockets
<b>Long Description:</b>	- This accessory is screwed into the tapped holes of the connector bar of the terminal blocks, - Compatible with test plugs DIA 2 mm 0.079 in.

## Ordering

<b>Color:</b>	Grey
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	74153300

## Dimensions

<b>Product Net Width:</b>	3.5 mm
<b>Product Net Height:</b>	5 mm
<b>Product Net Depth / Length:</b>	16 mm
<b>Product Net Weight:</b>	0.9 g

## Technical

<b>Spacing:</b>	2 mm
<b>Function:</b>	Test Sockets
<b>Recommended Screw Driver:</b>	3.5 mm
<b>Tightening Torque:</b>	Manufacturer 0.6 N·m

**Suitable For:**

D1.5/5.ADO.NF  
D1.5/6.ADO  
D1.5/6.ADO.NF  
D1.5/6.D2.ADO  
D1.5/6.D2.ADO.NF  
D2.5/8.ADO  
D2.5/8.ADO.NF  
D4/6.ADO  
D4/6.D2.ADO  
D4/8.ADO  
D4/8.ADO.NF  
D4/8.D2.P.SF  
D6/8.ADO  
D6/8.ADO.RS  
D6/8.D2.ADO  
M10/10  
M16/12  
M2.5/6.2G.2G  
M2.5/6.4G.1  
M2.5/6.5.4G.1  
M4/6  
M4/6.2G  
M4/6.3A  
M4/6.3A.NC  
M4/6.3G  
M4/6.4A  
M4/6.5.3G  
M4/6.G  
M4/6.RS  
M4/8.D2.SF  
M4/8.D2.SF.NC  
M6/8  
M6/8.D  
M6/8.D2.NC  
ML10/13.SF  
ML10/13.SN  
MU10/13.SF  
MU10/13.SN  
MU10/14.5.SF  
MU10/14.5.SN

**Environmental**

**Ambient Air Temperature:** Operation -55 ... +110 °C

**Classifications**

**Object Classification Code:** X

---

**E-number:** 2925663

**Container Information**

**Package Level 1 Units:** 50 piece

---

**Package Level 1 Gross Weight:** 0.045 kg

---

**Package Level 1 EAN:** 3472591630435

---

**Package Level 2 Units:** 10000 piece

