


Data sheet | Item number: 216-267

Ferrule; Sleeve for 4 mm² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



www.wago.com/216-267



Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Data

Technical data

| | |
|----------------------------|-------------------|
| Main product function | Ferrule |
| Sleeve cross-section (AWG) | 12 AWG |
| Sleeve for | 4 mm ² |

Connection data

| | |
|--------------|-------------------|
| Strip length | 14 mm / 0.55 inch |
|--------------|-------------------|

Physical data

| | |
|------------|--------|
| Length | 20 mm |
| Length 1 | 12 mm |
| Diameter | 5.4 mm |
| Diameter 1 | 4.8 mm |
| Diameter 2 | 2.8 mm |

Mechanical data

| | |
|----------|---------------------|
| Suitable | 2004 to 2006 Series |
|----------|---------------------|

Material data

| | |
|-----------|----------|
| Color | gray |
| Fire load | 0.001 MJ |
| Weight | 0.2 g |

Commercial data

| | |
|-------------------------------------|--------------------------------|
| Product Group | 2 (Terminal Block Accessories) |
| PU (SPU) | 500 (100) Pieces |
| Packaging type | box |
| Country of origin VKOrg Germany | DE |
| GTIN | 4055143654739 |
| Customs tariff number VKOrg Germany | 85369010000 |

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Downloads Documentation

Bid Text


| | | | |
|------------------------|--------------|----------------|----------|
| 216-267 X81 - Datei | Feb 19, 2019 | xml 2.9 kB | Download |
| 216-267 doc - Datei | Sep 11, 2017 | doc 24.6 kB | Download |

Environmental Product Compliance

Compliance Search

| | | |
|--|-----|----------|
| Environmental Product Compliance 216-267 Ferrule; Sleeve for 4 mm ² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray | URL | Download |
|--|-----|----------|

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable

Subject to changes. Please also observe the further product documentation!