




radiant Collection
Smart Switch With Netatmo Starter Kit, White
Part No. WNRH10KITWH



The smartest way to take control of lights and power, optimized for larger homes.

Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, dimmers and outlets to build a solution that perfectly fits a home's unique space and needs. Options include wireless smart switches and dimmers for easily adding 3-way control.

Features & Benefits

The foundation of a radiant with Netatmo solution, the in-wall Gateway easily replaces an existing switch or outlet to provide a discreet hub for a home's smart lighting control

Ensures ultra-reliable performance through a robust and dedicated mesh-network

Enables control of a home's smart lighting solutions through the Legrand Home + Control app, allowing for easy scheduling, the creation of groups, setting scenes, managing energy usage and more

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems

Flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets, including wireless switches and dimmers

Compatible with all radiant® with Netatmo and adorne® with Netatmo smart devices

Installs easily in place of an existing single-pole switch or dimmer (neutral wire required). For easy 3-way control, pair with a Wireless Smart Switch with Netatmo

Flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets, including wireless switches and dimmers

Available color options include White, Light Almond and Nickel

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look

Includes Smart Gateway

Specifications

General Info

| | | | |
|--------------------|-------------------------|------------------|---|
| Color | White | UPC Number | 785007276930 |
| Country Of Origin | China | Product Line | Pass & Seymour |
| Finish | Matte | Included | Gateway (WNRH2WH), Smart Switch (WNRL10WH), Wireless Battery (WNRL33WH) |
| Application Sector | Residential/Commercial | Type | Tamper-Resistant |
| Warranty Type | 1-Year Limited Warranty | Wall Plate Color | White |

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|---------------------|---------|
| cULus Listed | Yes | cULus ListingNumber | E350248 |
|--------------|-----|---------------------|---------|

Additional Information

| | | | |
|-----------------|-----|--------------------------|----|
| RoHS Conformant | Yes | Prop 65 Warning Required | No |
|-----------------|-----|--------------------------|----|

| | |
|---|-----|
| Product Has Potential to Contribute to LEED | Yes |
|---|-----|

Technical Information

| | | | |
|-----------------|-------------------|---------------|---|
| Number of Poles | Single Pole 3-Way | Compatibility | Amazon Alexa, Google Assistant, Apple HomeKit |
|-----------------|-------------------|---------------|---|

| | | | |
|----------------|-------|----------------|-------|
| Supply Voltage | 120 V | Number of Ways | 3-Way |
|----------------|-------|----------------|-------|

| | | | |
|----------------|------|-----------------|---|
| Current Rating | 15 A | Number of Wires | 3 |
|----------------|------|-----------------|---|

| | | | |
|-----------------|-------|----------------|--------------------------|
| Connection Type | Wired | Lighting Types | Incandescent/Halogen/LED |
|-----------------|-------|----------------|--------------------------|

| | |
|--------------------------|------------|
| Environmental Conditions | Indoor pct |
|--------------------------|------------|
