Thomas&Betts



Actual

Catalog Number:SProduct ID:7UPC Number:7EAN Number:6Status:6Replacement Catalog:7

SF175-50X-100 7TAG009700R0019 78621099668 05414363160861 Obsolete TY525MX

Low Profile In-Line Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant, Length of 200.53mm (7.895 Inches), Width of 4.75mm (0.187 Inches), Thickness of 1.22mm (0.048 inches), Tensile Strength Rating of 220 Newtons (50 pounds), 100 Pack

- Low-Profile, contoured head reduces clearance required for the bundle and enhances the appearance of your harness.
- The safeguard wall eliminates exposure to sharp edges.
- The saddleback fits snug against the contour of the wiring harness.

North American Specifications (UNSPSC)

North American Specifications (UNSF 5C)	
UNSPSC	39121703 Cable ties
IGCC	5041 Inline Ties
Brand Name	Safe-Ty
Туре	Low Profile
Special Features	Low-Profile, contoured head reduces clearance re-
	quired for the bundle and enhances the appearance
	of your harness.
Width	0.187 in ; 4.75 mm
Length	7.895 in ; 200.53 mm
Thickness	0.048 Inch/1.22mm
Bundle Diameter	0.185 Inch/4.7mm to 1.75 Inches/44.5mm
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	50 Pounds/220 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.75mm
Length belt/tape/tie	200.53mm
Tie thickness	1.22mm
Min. holding force	220N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	Ν
Reflective (fluorescent)	Ν
Text strip	None
Solvable fastener	Ν
MIL approval	Ν
Packaging	
Inner Quantity	100
Inner Dimensions (inches)	12x5x1.25
Outer Quantity	1000

Thomas&Betts

Outer Dimensions (inches) Weight Uom 9.89x6.7x7.9 2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA 860 Ridge Lake Blvd. Memphis, TN 38120 www.tnb.com ABB Installation Products Technical Support MS 3B-50 860 Ridge Lake Blvd. Memphis, TN 38120 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com