

APC Back-UPS Pro

Premium battery backup and surge protection for your critical devices

The new APC Back-UPS Pro models provide premium battery backup and surge protection. Ideal for small or home office electronics, networking devices, gaming PCs and consoles. APC Back-UPS Pro models provide sine wave output, USB charging ports for your mobile devices, and increased runtime for your critical electronics.



www.apc.com





APC Back-UPS Pro

Power and protect critical electronics and stay connected to the internet during outages, surges, and lightning



Sinewave power output

For advanced workstations, high end PCs, Smart TVs, multimedia devices, and home storage

2 USB charging ports (Type C+ Type A)

To maximize charging speeds and simultaneously charge mobile devices such as smartphones and tablets

Active PFC compatibility

For contemporary high end PCs and gaming users

6 Battery backup outlets

Keep more devices running when the power is outside of safe levels

LCD Display

Quick and easy to read, provides information about the utility and UPS conditions

1 Gb network and coax protection

Safeguards your equipment and valuable files from "back door" surges traveling along data lines without sacrificing internet speed

Powerchute personal edition

Easy-to-use auto-shutdown software with power and energy management features

Ideal for high performance devices such as:



PHONE











USB charging ports for your mobile devices such as:



Life Is Or







How much runtime will the Back-UPS Pro provide?					
Connected devices	Watt load	BR1000MS	BR1350MS	BR1500MS2	
Entry-level desktop with 20" monitor + internet modem and router	40 watts	92 minutes	110 minutes	150 minutes	
Notebook computer + network gateway + internet modem and router	79 watts	53 minutes	66 minutes	94 minutes	
Mid-range PC with 20" LCD + notebook + network gateway + internet modem and router	119 watts	36 minutes	46 minutes	66 minutes	
Gaming PC with 24" LCD monitor + external powered speakers + internet modem and router	240 watts	16 minutes	22 minutes	32 minutes	
42" LCD television + game console system (Xbox or PlayStation)	335 watts	10 minutes	14 minutes	21 minutes	
*Runtime and USB power will vary according to device(s), usage, and power settings.					



Life Is On

APC Back-UPS Pro technical specifications

Products specification	BR1000MS	BR1350MS	BR1500MS		
Output					
Output Capacity	1000VA / 600W	1350VA / 810W	1500VA / 900W		
Output Voltage / Frequency (On utility)	98 to 139Vac, 60Hz +/- 1Hz				
Output Voltage / Frequency (On battery)	115 Vac +/- 8%, 60Hz +/- 1Hz				
Output Connections	10 total NEMA5-15R outlets: 6 battery backup & surge and 5 surge only				
Waveform Type	Sine Wave				
Input					
Input Voltage / Frequency	120 Vac, 60Hz ± 3Hz				
Input Connection	Straight plug end with NEMA 5-15				
Input Cord	6 ft cord				
Surge Protection					
Surge Energy Rating	1080 Joules				
Data Line Surge Protection	1GB dataline protection: 1-in, 1 out Network line – 10/1000BT, coaxial				
Physical					
Unit Dimensions (H x W x D)		10.47 x 3.9 x 14.5 in.			
Unit Weight	22.48 lbs.	22.48 lbs.	27.55 lbs.		
Shipping Dimensions (H x W x D)	14.11 x 5.59 x 17.40 in.				
Shipping Weight	16.75 lbs.	17.63 lbs.	26.23 lbs.		
Color	Black				
Battery					
Battery Type	Sealed, lead-acid, maintenance-free				
Replacement Battery	APCRBC160	APCRBC161	APCRBC163		
Management	·				
Alarms	Visual (LCD display) and audible alarms				
Shutdown S/W	PowerChute Personal Edition (via USB interface)				
Warranty					
Standard Warranty Length		3 years			
Equipment Protection Policy	\$250,000	\$500,000			
Certification/Approvals					
TU	V C-US certified, ENERGY ST	AR™, CEC, DOE, NOM			

132 Fairgrounds Road West Kingston, RI 02892 United States Phone: +1 800-800-4272 www.apc.com



Life Is On

© 2020 Schneider Electric. All Rights Reserved. Schneider Electric | Life Is On is a trademark and the property of Schneider Electric SE, its subsidiaries, and affiliated