

Rackshelves

Universal Rackshelves

These easy-to-install universal shelves accommodate components up to 17³/₈" wide. Made from 16-gauge steel, finished in a durable black powder coat and individually boxed.

| Part # | Racking Height | Useable Shelf Area | Capacity | Self Merchandising Rackshelf Packs | |
|--------|---|---------------------|----------|------------------------------------|----------|
| | | | | Part # | Quantity |
| U1 | 1 ³ / ₄ " (1 space) | 17.44" w x 10.72" d | 35 lbs. | U1-RP12 | 12 U1s |
| U2 | 3 ¹ / ₂ " (2 space) | 17.44" w x 14.50" d | 50 lbs. | U2-RP6 | 6 U2s |
| U3 | 5 ¹ / ₄ " (3 space) | 17.44" w x 14.50" d | 70 lbs. | | |
| U4 | 7" (4 space) | 17.44" w x 15.44" d | 85 lbs. | | |

Display U1 and U2 rackshelves in a retail location or will-call area.

SH Series Zero Space Rackshelves

These 4 point mount shelves have been purpose designed to fit in Slim 5 (pgs. 32-33), AXS (pgs. 49-51), SRSR (pg. 52) and WR (pg.48) equipment racks, and feature full-depth front and rear rackmounting to provide a secure shelf for non-rackmount components. The models designated for the Slim 5, AXS and SRSR mount to the sides of the rackrail, while the SH-WR features an enhanced, patent pending design that mounts to the threaded rail - while still utilizing zero rackspaces! Two handy "L" brackets are included to help position equipment. Constructed from 16-gauge steel, includes mounting hardware and finished in a durable black powdercoat.

| Part # | Useable Shelf Area | Weight Capacity | Fits |
|---------------------|---------------------|-----------------|--------------------------------|
| SH-5A* | 18.50" w x 18.57" d | 250 lbs. | 20" depth AXS & Slim 5 racks |
| SH-5A-26* | 18.50" w x 24.57" d | 250 lbs. | 26" depth AXS & Slim 5 racks |
| SH-SRSR** | 18.44" w x 15.50" d | 200 lbs. | SRSR racks |
| SH-WR | 18.70" w x 22.75" d | 250 lbs. | WR-xx-32 racks ENHANCED |
| NEW SH-WR-34 | 18.70" w x 32.75" d | 250 lbs. | WR-xx-42 racks |

*SH-5A, SH-5A-26 does not mount in the top or bottom 2 rackspaces, or where rackrail brackets are located. **SH-SRSR does not mount in the bottom 5 rackspaces, or where rackrail brackets are located.

Vented 3 Space Rackshelf

17³/₄" deep by 5¹/₄" high, this vented rackshelf has a 60 lb. weight capacity and a rear flange slotted for horizontal cable management. Constructed from 16-gauge steel and finished in a black powder coat.


| Part # | Racking Height | Useable Shelf Area | Weight Capacity |
|--------|---|---------------------|-----------------|
| U317 | 5 ¹ / ₄ " (3 space) | 17.44" w x 17.50" d | 60 lbs. |

23" Panel Width Version

| Part # | Racking Height | Useable Shelf Area | Weight Capacity | Panel Width |
|---------|---|---------------------|-----------------|-------------|
| U317-23 | 5 ¹ / ₄ " (3 space) | 21.44" w x 17.40" d | 60 lbs. | 23" |

Vented 2 Space Center-Mount Shelf

Ideal for use in our open frame racks (pgs. 56-59), this vented 3¹/₂" (2 space) shelf is 18" deep with a 50 lb. weight capacity. Constructed from 16-gauge steel and finished in a durable black powder coat.

| Part # | Racking Height | Useable Shelf Area | Weight Capacity | U2MS shown mounted on open frame rack |
|--------|---|--------------------|-----------------|---|
| U2MS | 3 ¹ / ₂ " (2 space) | 17.41" w x 18" d | 50 lbs. |  |

Half/Third-Rack Shelf

Mount smaller components, wireless units and other gear horizontally w/ the UTR1 half/third-rack shelf. Now includes hook-and-loop strips for component mounting, and features an enhanced ventilation pattern. Constructed from 16-gauge steel with a 25 lb. weight capacity and finished in a durable black powder coat.

| Part # | Racking Height | Useable Shelf Area | Weight Capacity | Self Merchandising Rackshelf Packs | |
|--------|---|--------------------|-----------------|------------------------------------|----------|
| | | | | Part # | Quantity |
| UTR1 | 1 ³ / ₄ " (1 space) | 17.38" w x 10" d | 25 lbs. | UTR1-RP12 | 12 UTR1s |


This attractive rackshelf pack displays UTR1 rackshelves in a retail location or will-call area.



U2



U2-RP6



brackets prevent components from sliding backwards

ENHANCED MOUNTING


SH-WR, SH-WR-34

SH-5A, SH-5A-26, SH-SRSR attaches to side of rackrail behind front rail face



cable lacing slots built-in

U317




cable lacing slots built-in

U2MS



UTR1-RP12



UTR1