

Pilot and Signaling Devices

Heavy-Duty 30.5 mm Watertight/Oiltight Accessories

Section 9


CR104P

Nameplates and Legend Inserts
600 Volts max. AC/DC
10 Amperes Continuous


Nameplates—Standard Lithographed

Unless otherwise indicated, all nameplates are black and available in Sizes 1-3 only. To select size, replace asterisk (*) in product number with appropriate digit from Sizes table.


Nameplate Marking	Product Number
Blank (Sizes 1-5)	CR104PXN*B
Blank (Red, sizes 1-5)	CR104PXN*R
Blank (with round)	CR104PXN6E
CLOSE	CR104PXN*BP006
DECREASE	CR104PXN*BP007
DOWN	CR104PXN*BP008
EMERGENCY STOP (Red)	CR104PXN*RP009
FAST	CR104PXN*BP010
FORWARD	CR104PXN*BP011
HIGH	CR104PXN*BP012
IN	CR104PXN*BP013
INCH	CR104PXN*BP014
INCREASE	CR104PXN*BP017
JOG	CR104PXN*BP018
JOG FORWARD	CR104PXN*BP019
JOG REVERSE	CR104PXN*BP020
LEFT	CR104PXN*BP021
LOW	CR104PXN*BP022
LOWER	CR104PXN*BP023
OFF	CR104PXN*BP024
ON	CR104PXN*BP025
OPEN	CR104PXN*BP026
OUT	CR104PXN*BP027
POWER ON	CR104PXN*BP084
RAISE	CR104PXN*BP028
RESET	CR104PXN*BP030
RETURN	CR104PXN*BP031
REVERSE	CR104PXN*BP032
RIGHT	CR104PXN*BP033
RUN	CR104PXN*BP034
SLOW	CR104PXN*BP036
START	CR104PXN*BP037
START CYCLE	CR104PXN*BP038
STOP (Red)	CR104PXN*RP040
STOP CYCLE (Red)	CR104PXN*RP041
TEST	CR104PXN*BP043
UP	CR104PXN*BP047
EMERGENCY STOP PULL TO TEST (Red)	CR104PXN*RP048
PUSH TO STOP PULL TO START	CR104PXN*BP085
FOR REV	CR104PXN*BP050
HAND AUTO	CR104PXN*BP051
HIGH LOW	CR104PXN*BP052
JOG RUN	CR104PXN*BP053
LEFT RIGHT	CR104PXN*BP054
LOW HIGH	CR104PXN*BP055
LOWER RAISE	CR104PXN*BP056
OFF ON	CR104PXN*BP057
OPEN CLOSE	CR104PXN*BP058
RAISE LOWER	CR104PXN*BP059
REV FOR	CR104PXN*BP060
RUN JOG	CR104PXN*BP061
SAFE RUN	CR104PXN*BP062
SAFE STOP RUN	CR104PXN*BP063
SLOW FAST	CR104PXN*BP064
START JOG	CR104PXN*BP087
START STOP	CR104PXN*BP086
STOP START	CR104PXN*BP065
UP DOWN	CR104PXN*BP066
OFF COOLANT ON	CR104PXN*BP067
AUTO OFF-HAND	CR104PXN*BP083
FOR OFF REV	CR104PXN*BP068
FOR STOP REV	CR104PXN*BP069
HAND OFF AUTO	CR104PXN*BP070
JOG OFF RUN	CR104PXN*BP071
JOG SAFE RUN	CR104PXN*BP072
LOW OFF HIGH	CR104PXN*BP073
LOWER OFF RAISE	CR104PXN*BP074
MAN OFF AUTO	CR104PXN*BP076
OPEN OFF CLOSE	CR104PXN*BP077
REV OFF FOR	CR104PXN*BP079
SLOW OFF FAST	CR104PXN*BP080
SLOW STOP FAST	CR104PXN*BP081
POTENTIOMETER MARKINGS	CR104PXN*BP082
OFF AUTO	CR104PXN1BP090
ON OFF AUTO	CR104PXN1BP091
PUSH TO STOP - TURN TO RESET (Round w/Yellow Background)	CR104PXN6EP092
Yellow Background Emergency Stop	CR104PXN6EP009




Standard (Size 1)




Large (Size 2)



Extra-large Automotive (Size 3)



Small Joystick (Size 4; available for XN*R and XN*B only)



Large Joystick (Size 5; available for XN*R and XN*B only)

Sizes*

Nameplate	Dimensions (H x W, Inches)	*Product No. Digit
Standard (Size 1)	1.98 x 1.93	1
Large (Size 2)	1.98 x 2.63	2
Extra-large, automotive (Size 3)	2.40 x 2.44	3 ¹
Small joystick (Size 4; available for XN*R and XN*B only)	2.32 x 2.32	4 ¹
Large joystick (Size 5; available for XN*R and XN*B only)	2.92 x 2.92	5 ¹

¹These nameplates do not fit standard enclosures.

