



**SKU:** ELT-7

**UPC:** 0783669257427

**Features & Benefits:**

**Description:** Permagraund Copper Grounding E Crimp, Main Conductor Range 500-300, Main Rebar Size #5, Tap Range 3/0-6 Sol, Tap Rebar Size #3-#4, UL, CSA

## Specs

### Additional Class Attributes

|                         |      |
|-------------------------|------|
| Fixing Type             | NA   |
| ILSCOs Die Index Number | 1011 |

### Conductor Ranges

|  |                       |
|--|-----------------------|
| Conductor Range CU Solid (Primary, run, main, line)    | NA                    |
| Conductor Range CU Solid (Secondary, tap, load)        | 2 Sol - 6 Sol         |
| Conductor Range CU Stranded (Primary, run, main, line) | 500 kcmil - 300 kcmil |
| Conductor Range CU Stranded (Secondary, tap, load)     | 3/0 Str - 6 Str       |
| Ground Rod Size  | 5/8                   |
| Rebar Size(s) Main                                     | #5 (5/8)              |
| Rebar Size(s) Secondary                                | #4 (1/2)              |

### Dimensions

|                |         |
|----------------|---------|
| Height (IN)    | 2.672   |
| Height BX (IN) | 2       |
| Height (mm)    | 67.8688 |
| Length (IN)    | 1.325   |
| Length (mm)    | 33.655  |
| Weight (LB)    | 0.505   |
| Weight BX (LB) | 3.1     |
| Width (IN)     | 0.875   |
| Width BX (IN)  | 5       |
| Width (mm)     | 22.225  |

### Material and Finish

|                    |        |
|--------------------|--------|
| Conductor Material | Copper |
| Connector Finish   | Bare   |
| Material           | Copper |

### Additional Technical Specifications

|                |       |
|----------------|-------|
| Conductor Type | Solid |
|----------------|-------|

### General

|                             |                |
|-----------------------------|----------------|
| Bag Quantity                | 1              |
| Carton Quantity Description | STD PACK QTY 6 |
| Direct Burial               | Yes            |
| Dual Rated                  | No             |
| NEMA Code                   | S-573-3        |
| UPC Code                    | 78366925742    |

### Testing Standards

|                          |   |
|--------------------------|---|
| Prop65 Compliance        | This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation |
| UL / CULUS Specification | UL 467 Listed   |

### Environment and Temperature

|                    |    |
|--------------------|----|
| Temperature Rating | NA |
|--------------------|----|

### Color

|       |        |
|-------|--------|
| Color | Copper |
|-------|--------|