

# NON-CONTACT VOLTAGE TESTERS

DETECT PRESENCE OF AC VOLTAGE

- UL Listed
- CAT IV 1000V AC & CAT IV 600V AC models
- Dual and Single Range Models
- IP67 Dust Tight/Water Immersion Protection\* (61-657 & 61-647)
- 2 Meter drop protection (61-657 & 61-647)
- Bright LED forward facing flashlight (3 models)



BUILT-IN  
FLASHLIGHT



**61-657**  
Dual Range  
12 to 1000V AC  
NCVT w/Flashlight  
CAT IV 1000V

BUILT-IN  
FLASHLIGHT



**61-647**  
Single Range  
50 to 1000V AC  
NCVT w/Flashlight  
CAT IV 1000V

BUILT-IN  
FLASHLIGHT



**61-637**  
Single Range  
24 to 600V AC  
NCVT w/Flashlight  
CAT IV 600V



**61-627**  
Single Range  
50 to 600V AC  
NCVT  
CAT IV 600V



Lanyard Tie-off

Power  
On/Off

Audible  
On/Off

Pocket Clip

Dual  
Sensitivity Range

Flashlight  
On/Off



Lanyard Tie-off

Power  
On/Off

Audible  
On/Off

Pocket Clip

Flashlight  
On/Off



\*Protection against the effects of water immersion in water between 5.9 in. (15cm) and 39.37 (1m) for 30 minutes.

THE ELECTRICIAN'S  
**CHAMPION**™



# NON-CONTACT VOLTAGE TESTERS

NON-CONTACT VOLTAGE TESTER SELECTION GUIDE	 NEW	 NEW	 NEW	 NEW
FEATURES	61-657	61-647	61-637	61-627
CAT Rating (Safety)	CAT IV 1000V	CAT IV 1000V	CAT IV 600V	CAT IV 600V
Listing	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM
Voltage Sensing Range	12 ~ 1000V AC	50 ~ 1000V AC	24 ~ 600V AC	50 ~ 600V AC
Dual Range	✓	—	—	—
Flashlight	✓	✓	✓	—
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)	3.3 ft. (1m)	3.3 ft. (1m)
Ingress Protection	IP67	IP67	—	—
Dual Range Sensitivity	✓	—	—	—
Audible Indication	✓	✓	✓	✓
Audible Defeat	✓	✓	✓	—
Visual Indication	Green On, Flashing Red	Green On, Flashing Red	Green On, Flashing Red	Green On, Flashing Red
Visual Range Indicator	Blue Low, Red High	—	—	—
Lanyard Compatible	✓	✓	✓	✓
Auto-Power Off (APO)	✓	✓	✓	✓
Low Battery Indication	✓	✓	✓	✓
Battery Type	2 x 1.5V AAA	2 x 1.5V AAA	2 x 1.5V AAA	2 x 1.5V AAA
Warranty	2-Year	2-Year	2-Year	2-Year



Scan with your smartphone to learn more




**Detects AC voltage at outlets**  
(including TR's w/61-657)



**Detects AC voltage on conductors**



**Detects AC voltage at panels**



**2 x 1.5V AAA Batteries**  
(Included)

P-6044 (5-21)  
©2021 IDEAL INDUSTRIES, INC.

**IDEAL CUSTOMER SERVICE:**  
orderdesk@idealindustries.com  
**1-800-824-3325**  
www.idealind.com

THE ELECTRICIAN'S  
**CHAMPION™**

