



Quality Products. Service Excellence.


## C2 Doors *CDF Series*

Exclusively for use with the C2 Cabinet Series



### Features

- Constructed in 16-gauge steel.
- Easily installs into **C2 Series** cabinets using integrated spring pin at top and bottom of the door.
- Includes formed plastic handle, quarter-turn lock and hinges to mount on the cabinet.
- Available in Solid, Windowed and Perforated and Split Perforated options.
- Finished in textured RAL9005 black or RAL7035 light gray powder paint finish.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.



### Accessories

- Door Adapter Kit
- Cabinet Door Replacement Lock
- Partial Height Door Support



Door Type	Part No.	Part No.	Use with Cabinet	
	Black	RAL 7035 Light Gray	Rack Units	Height
Solid	CDF1935SBK1	CDF1935SLG1	20U	35.00
	CDF1942SBK1	CDF1942SLG1	24U	42.00
	CDF1949SBK1	CDF1949SLG1	28U	49.00
	CDF1956SBK1	CDF1956SLG1	32U	56.00
	CDF1963SBK1	CDF1963SLG1	36U	63.00
	CDF1970SBK1	CDF1970SLG1	40U	70.00
	CDF1978SBK1	CDF1978SLG1	45U	78.75
	CDF1985SBK1	CDF1985SLG1	49U	85.75
Louver Vented Door	CDF1935LBK1	CDF1935LLG1	20U	35.00
	CDF1942LBK1	CDF1942LLG1	24U	42.00
	CDF1949LBK1	CDF1949LLG1	28U	49.00
	CDF1956LBK1	CDF1956LLG1	32U	56.00
	CDF1963LBK1	CDF1963LLG1	36U	63.00
	CDF1970LBK1	CDF1970LLG1	40U	70.00
	CDF1978LBK1	CDF1978LLG1	45U	78.75
	CDF1985LBK1	CDF1985LLG1	49U	85.75
Vented Door	CDF1970VBK1	CDF1970VLG1	40U	70.00
	CDF1978VBK1	CDF1978VLG1	45U	78.75
Window Door	C2DF1935PBK1	Not Available	20U	35.00
	C2DF1942PBK1	Not Available	24U	42.00

Door Type	Part No.	Part No.	Use with Cabinet	
	Black	RAL 7035 Light Gray	Rack Units	Height
	C2DF1949PBK1	Not Available	28U	49.00
	C2DF1956PBK1	Not Available	32U	56.00
	C2DF1963PBK1	Not Available	36U	63.00
	C2DF1970PBK1	<b>C2DF1970PLG1</b>	40U	70.00
	C2DF1978PBK1	Not Available	45U	78.75
	C2DF1985PBK1	Not Available	49U	85.75
Vented Window Door	CDF1970VPBK1	<b>CDF1970VPLG1</b>	40U	70.00
	CDF1978VPBK1	<b>CDF1978VPLG1</b>	45U	78.75

*Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.