SATCO NUVO

Project Name

Location

Prepared By



Notes

www] 11-22-2021 02:57:4

General	
Status	Active
Watts	
	60W 500W
Incandescent Equivalent	85W
Fluorescent Equivalent HID Equivalent	250W
Volts	100V-277V
	Corncob
Shape	
ANSI Base	Mogul Extended EX39
Finish	Clear
CCT (Kelvin)	5000
Temperature CRI	Natural Light 80
	8400L
Lumens	
Beam Spread	120;150;260
Dimmable Hours Pated	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED Denth 0.20 in
Min Compartment Size	Width: 9.30 in. Depth: 9.30 in. Height: 9.80 in.
Electrical	
Operating Frequency	50/60 Hz
Power Factor	>0.9
Surge Protection	Built-in surge protection - 4KV
THD	<20%
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)
Physical	
MOL	7.76
MOD	4.13
Lens Finish	Clear
Lens Material	Thermo Plastic (PBT)
Housing Color	White
Photocell	Optional Add-On
Weight (lb.)	2.05
Additional Information	
Additional Information Additional Info	PIR Sensor available as an accessory
	PIR Sensor available as an accessory Yes
Additional Info	accessory
Additional Info Rated For Enclosed Fixture	accessory Yes
Additional Info Rated For Enclosed Fixture IP Rating	Yes IP64 Closed 260 deg; Partial 150 deg;
Additional Info Rated For Enclosed Fixture IP Rating Specification Note	accessory Yes IP64 Closed 260 deg; Partial 150 deg; Open 120 deg
Additional Info Rated For Enclosed Fixture IP Rating Specification Note Warranty	accessory Yes IP64 Closed 260 deg; Partial 150 deg; Open 120 deg
Additional Info Rated For Enclosed Fixture IP Rating Specification Note Warranty Compliance	accessory Yes IP64 Closed 260 deg; Partial 150 deg; Open 120 deg 5 Year Limited - Hi-Pro
Additional Info Rated For Enclosed Fixture IP Rating Specification Note Warranty Compliance Safety Listing Location Rating	accessory Yes IP64 Closed 260 deg; Partial 150 deg; Open 120 deg 5 Year Limited - Hi-Pro cULus Classified
Additional Info Rated For Enclosed Fixture IP Rating Specification Note Warranty Compliance Safety Listing	accessory Yes IP64 Closed 260 deg; Partial 150 deg; Open 120 deg 5 Year Limited - Hi-Pro cULus Classified Damp

DLC ID	PL1DH99JBHHE
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: http://www.satco.com/







