



# LED Highbay

## 165HB/LED/840/ND WB UDL 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

### Product data


General Information	
Base	EX39 [ Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	165-400W
Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	120 °
Initial lumen (Nom)	19000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115.15 lm/W
Color Consistency	ANSI 4000K
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	165 W
Lamp Current (Nom)	3650 mA
Wattage Equivalent	400 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	Type A - works on ballast
Power Factor (Nom)	0.6
Voltage (Nom)	52-58 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Others
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	165HB/LED/840/ND WB UDL 2/1
EAN/UPC - Product	046677465674
Order code	465674
Numerator - Quantity Per Pack	1

# LED Highbay

Numerator - Packs per outer box	2
Material Nr. (12NC)	929001265504
Net Weight (Piece)	1.300 kg



## Dimensional drawing



**Bulb 135W-400W 16000lm 120D 4000K E39XND**


Product	D	C
165HB/LED/840/ND WB UDL 2/1	209.7 mm	245.7 mm

## Photometric data



**NAM Highbay 165W-400W 4000K 120D E39X UDL**



**NAM Highbay 165W EX39 4000K 60-120D NB WB UDL**



**NAM Highbay 165W EX39 4000K 120D WB UDL**

# LED Highbay

## Lifetime



NAM Highbay 165W EX39 4000K 60-120D DL UDL

NAM Highbay 165W EX39 4000K 60-120D DL UDL

