

## Rigid Conduit

### Pull Elbows and Conduit Fittings



**CI7204 / CI7206**



Zinc Die Cast Locknut

**CI7304 (-G) / CI7310 (-G)**




-G: with gasket

**CICA-1/2 / CICA-2**



**CICA-2-1/2 / CICA-4**



**CILRL-1/2 / CILRL-2**



Supplied with 2 covers

**CILL-2 1/2 / CILL-4**



**CILR-2 1/2 / CILR-4**



Cat. No.	Trade Size (in.)	Dimensions (in.)		
		A	B	C
<b>Pull Elbows, Rigid to Box (Zinc Alloy)</b>				
CI7204	1/2	1-5/16	1-1/8	—
CI7206	3/4	1-5/8	1-5/16	
<b>Pull Elbows, Rigid to Rigid (Zinc Alloy)</b>				
CI7304	1/2	1-5/16	1-1/8	—
CI7306	3/4	1-7/16	1-5/16	
CI7304-G	1/2	1-5/16	1-1/8	
CI7306-G	3/4	1-7/16	1-5/16	
CI7308-G	1	2	1-5/8	
CI7310-G	1-1/4	2-1/4	2	
<b>Rigid Conduit Fittings - "C" Type (Cast Aluminum)</b>				
CICA-1/2	1/2	4-7/8	1-3/8	1-3/8
CICA-3/4	3/4	5-9/16	1-1/2	1-7/16
CICA-1	1	6-1/2	1-3/4	1-3/4
CICA-1-1/4	1-1/4	8-5/8	1-15/16	2-1/2
CICA-1-1/2	1-1/2	8-5/8	2-11/16	2-1/2
CICA-2	2	10-15/16	3	3-3/16
CICA-2-1/2	2-1/2	12-3/4	5-1/8	4-1/4
CICA-3	3	12-3/4	5-1/8	4-1/4
CICA-3-1/2	3-1/2	15	6-1/2	5-1/4
CICA-4	4	15	6-1/2	5-1/4
<b>Rigid Conduit Fittings - "LRL" Type (Cast Aluminum)</b>				
CILRL-1/2	1/2	4-7/16	1-11/16	2-1/8
CILRL-3/4	3/4	5-3/16	1-7/8	2-1/4
CILRL-1	1	6	2-3/16	2-1/2
CILRL-1-1/4	1-1/4	7-15/16	2-3/4	3-1/2
CILRL-1-1/2	1-1/2	7-15/16	3-1/4	3-1/2
CILRL-2	2	10-3/16	3-11/16	4-1/8
<b>Rigid Conduit Fittings - "LL" Type (Cast Aluminum)</b>				
CILL-2 1/2	2-1/2	12-1/4	5-1/8	5-3/4
CILL-3	3	12-1/4	5-1/8	5-3/4
CILL-3 1/2	3-1/2	14-3/8	6-1/4	6-3/4
CILL-4	4	14-3/8	6-1/4	6-3/4
<b>Rigid Conduit Fittings - "LR" Type (Cast Aluminum)</b>				
CILR-2 1/2	2-1/2	12-1/4	5-1/8	5-3/4
CILR-3	3	12-1/4	5-1/8	5-3/4
CILR-3 1/2	3-1/2	14-3/8	6-1/4	6-3/4
CILR-4	4	14-3/8	6-1/4	6-3/4

Gaskets and covers are included with all rigid conduit fittings  
CICA-1/2 to CICA-2 and all CILRL are also suitable for use with EMT conduit