



S22215

8.5PAR30L/LED/940/FL/120V

GENERAL SPECIFICATIONS

Shape:	PAR 30L
Wattage:	8.5WW
Lumen Output:	700LL
Color Temperature:	4000K
Base:	Medium
Beam Spread:	40D



TECHNICAL SPECIFICATIONS

Wattage:	8.5W	Color Temperature:	4000K
Volts:	120V	CRI:	90CRI
Incandescent Equivalent:	75W	Lumen Output:	700L
Shape:	PAR 30L	Dimmable:	Yes-Dimmable
Filament:	LED	Dimming Function:	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Base:	Medium	Beam Spread:	40D
ANSI Base:	E26	Power Factor:	0.7
Finish:	Clear	Operating Temp:	-20C (-4F) to a maximum of +45C (+113F)
Housing Color:	White	Enclosure Rating:	Enclosed Rated Lamp
Hours Rated:	15000H	Safety Listing:	cULus Listed
Beam Spread:	40D	Technology:	LED
		Material:	Plastic; Aluminum

DIMENSIONS

MOL:	4.41"
MOD:	3.74"
Weight:	0.04

LISTINGS

ES Lamp Category:	Directional
Safety Listing:	cULus Listed
Location Rating:	Wet
Energy Star:	Yes
ES Unique ID:	ESID-2382246
UL File Listing:	E335148
Title 20:	Yes
CEC Terse:	Lawful for sale in California
RoHS Compliant:	Yes
FCC Compliant:	Yes
SDS Class:	LED_Lamp

PACKAGING

Each UPC:	045923210488	Inner UPC:	20045923210482	Case UPC:	10045923210485
Each Quantity:	1	Inner Quantity:	6	Case Quantity:	12
Each Dimensions:	3.90 x 3.90 x 4.80"	Inner Dimensions:	12.20 x 8.27 x 5.12"	Case Dimensions:	17.13 x 12.80 x 5.91"

110 Heartland Blvd.
Brentwood, NY 11717
PH 631-243-2022
FX 631-243-2027

Distribution Centers
New York, Florida,
Texas, Washington,
California, Puerto Rico

National Toll-Free
800-43-SATCO
(800-437-2826)
www.satco.com

Copyright 2021
Satco Products, Inc.
All Rights Reserved
October 24, 2021

COMPATIBLE DIMMERS

Brand	Model #
Cooper	SAL06P
Cooper	RF9640-ND
Cooper	DUL06P-C2
Cooper	DAL06P-C2
Cooper	SUF7
Cooper	TAL06P-C2
Cooper	VSUL06D
Legrand	ADTP703TU
Legrand	RHCL450PTC
Legrand	RH703PTUTC
Leviton	DDMX1
Leviton	DW6HD
Leviton	IPE04-1L
Leviton	66ELV
Lutron	PD-6WCL
Lutron	MSCL-OP153M
Lutron	RCL-153PNL
Lutron	RRD-6CL
Lutron	RRD-PRO
Lutron	PD-10WX
Lutron	NTRP-250
Lutron	NTCL-250
Lutron	MACL-153M
Lutron	MA-PRO
Lutron	LECL-153PH
Lutron	DVRP-253P
Lutron	DVCL-153P
Lutron	CTRP-253P
Lutron	AYCL-153P
Satco	S11268
Satco	86/103

110 Heartland Blvd.
 Brentwood, NY 11717
 PH 631-243-2022
 FX 631-243-2027

Distribution Centers
 New York, Florida,
 Texas, Washington,
 California, Puerto Rico

National Toll-Free
 800-43-SATCO
 (800-437-2826)
www.satco.com

Copyright 2021
 Satco Products, Inc.
 All Rights Reserved
 October 24, 2021