

WATTSTOPPER®

radiant[®] Incandescent Dimmer 700W & 1100W Incandescent Dimmer


RH1103PTC

Energy-saving dimming Incandescent loads.

RH703PW/RH703PTC, RH1103PW/RH1103PTC

radiant[®] dimmers help save energy simply, and as part of the radiant collection, now offer a better fit, form and finish. Compatible with incandescent dimmable bulbs, these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.

Features & Benefits



3rd Party Compliance

CULus listed, UL1472, CSA



WATTSTOPPER® radiant® Incandescent Dimmer 700W & 1100W Incandescent Dimmer

Technical Information

Performance

Electrical	
Supply Voltage	120VAC
Ratings	700W; 1100W Incandescent
Frequency	60Hz
Installation	Single Pole or 3-Way (Flying Leads)
Environmental	
Application	Indoor Use Only
Mechanical	
Enclosure Material	Polycarbonate



Warranty

Lifetime



700W & 1100W Incandescent Dimmer

Ordering Information

radiant® Incandescent Dimmers

Catalog Number	Description	Color	Voltage	Rating
RH703PTC	Preset, Single Pole and 3-Way	Three interchangeable Face Colors: Ivory, White, Light Almond	120VAC 60Hz	700W Inc
RH703PW	Preset, Single Pole and 3-Way	Face Color: White	120VAC 60Hz	700W Inc
RHKIT		Brown		
RHKITBK	-	Black		
RHKITGRY		Gray		
RHKITI	- - Interchangeable Faces -	lvory		
RHKITLA		Light Almond		
RHKITNI		Nickel		
RHKITW	-	White		
RHKITDB	-	Dark Bronze		
RH1103PTC	Preset, Single Pole and 3-Way	Three interchangeable Face Colors: Ivory, White, Light Almond	120V AC 60Hz	1100W Inc
RH1103PW	Preset, Single Pole and 3-Way	Face Color: White	120V AC 60Hz	1100W Inc
RHKIT		Brown		
RHKITBK	_	Black		
RHKITGRY	_	Gray		
RHKITI	Interchangeable For	lvory		
RHKITLA	 Interchangeable Faces 	Light Almond		
RHKITNI	_	Nickel		
RHKITW	_	White		
RHKITDB	-	Dark Bronze		



WATTSTOPPER[®]

radiant[®] Incandescent Dimmer 700W & 1100W Incandescent Dimmer

Vertical Markets

 Office Residential • Multiple Dwelling Hospitality/Lodging Also available in the radiant[®] collection Paddle Switches • Timers GFCI Receptacles Night Lights • Fan Controls • Screwless Wall Plates • Tamper-Resistant • Home Automation Controls and Standard Duplex Sensors • USB Charging Devices **Receptacles**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us 570 Applewood Crescent

Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca

