

# Definite Purpose Controls Full Voltage Starters

## CR553, CR353E/F/G

Standard

Accessories

25A-40A

### Auxiliary Contact Kits

Contactor Prefix	Contactor Rating	Description	Product Number
CR553	25A-40A 2-3 pole	250V, Side Mounted, SPDT	CR553XC211
CR553	25A-40A 2-3 pole	250V, Side Mounted, Two SPDT	CR553XC222
CR553	25A-40A 2-3 pole	DIN Rail Clip (sold only in multiples of 10)	CR553XDCA
CR353F	50A-60A	SPDT	CR353XAAA
CR353F	75A-90A	SPDT	CR353XAAB
CR353G	120A-150A	1NO-1NC	CR353XADC

### C-2000 Accessories

For more information, see the C-2000 Contactors and Starters Purchasing Guide (DEP-014). For use with CR45\* devices.


Accessory Type	Mounting Type	Contact Configuration	Type of Kit	Product Number
Auxiliary Contact Blocks	Front-Mount	1NO	—	BCLF10
Auxiliary Contact Blocks	Front-Mount	1NC	—	BCLF01
Auxiliary Contact Blocks	Side-Mount	1NO-1NC	—	BCLL11
Auxiliary Contact Blocks	Side-Mount	2NO	—	BCLL20
Mechanical Interlock	—	2NC	—	BELA02
Miscellaneous Kits	—	—	35 mm DIN Rail (1 meter)	CLXR35

### Overload Relays

Direct mount, manual/auto reset (stop/reset only). Requires contactor with sems clamp terminal (without quick connects) on load side. Select M for Digit 11 on page 4-7.

Current Range Amps(min-max)	Maximum Fuse Rating Amps	Maximum Circuit Breaker Rating Amps	Trip Class	Product Number
0.16-0.26	1	15	Class 10	RT1B
0.25-0.41	1	15	Class 10	RT1C
0.4-0.65	3	15	Class 10	RT1D
0.65-1.1	6	15	Class 10	RT1F
1-1.5	6	15	Class 10	RT1G
1.3-1.9	6	15	Class 10	RT1H
1.8-2.7	10	15	Class 10	RT1J
2.5-4.1	15	15	Class 10	RT1K
4-6.3	20	15	Class 10	RT1L
5.5-8.5	25	15	Class 10	RT1M
8.0-12.0	40	30	Class 10	RT1N
10.0-16.0	50	35	Class 10	RT1P
14.5-18	60	40	Class 10	RT1S
17.5-22	70	50	Class 10	RT1T
21-26	80	60	Class 10	RT1U
25-32	100	80	Class 10	RT1V
30-40	100	80	Class 10	RT1W
2.5-4.1	15	15	Class 20	RT12K
4-6.3	20	15	Class 20	RT12L
5.5-8.5	25	15	Class 20	RT12M
8.0-12.0	40	30	Class 20	RT12N
10.0-16.0	50	35	Class 20	RT12P
14.5-18	60	40	Class 20	RT12S
17.5-22	70	50	Class 20	RT12T
21-26	80	60	Class 20	RT12U
25-32	100	80	Class 20	RT12V
30-40	100	80	Class 20	RT12W

## Section 4



Auxiliary Contact Kits




Front-Mount Auxiliary Contact Block



Mechanical Interlock



DIN-Rail Kit



Overload Relay, Class 10

