



2488SW8804



541901



2577SW000H



2577SW000X



547703

EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
540836**	14/3	STW	3'	0.9 m	Red/Black	15	12
541901**	14/3	SJTW	22'	7 m	Red/Black	15	6
2487SW8804	14/3	SJTW	25'	7.6 m	Red	15	12
2488SW8804	14/3	SJTW	50'	15.2 m	Red	15	6
541902**	14/3	SJTW	50'	15.2 m	Red/Black	15	5
54800401**	14/3	SJTW	50'	15.2 m	Neon Pink	13	13
521*	14/3	SJTW	50'	15.2 m	Yellow/Black	15	13
2489SW8804	14/3	SJTW	100'	30.5 m	Red	13	6
541909**	14/3	SJTW	100'	30.5 m	Red/Black	15	3
2577SW000H	12/3	SJTW	25'	7.6 m	Cool Blue	15	12
2577SW000X	12/3	SJTW	25'	7.6 m	Cool Green	15	12
547703**	12/3	SJTW	25'	7.6 m	Dark Green/Yellow	15	12
2577SW000A	12/3	SJTW	25'	7.6 m	Cool Pink	15	12
2587SW8802	12/3	SJTW	25'	7.6 m	Yellow	15	12
2578SW000H	12/3	SJTW	50'	15.2 m	Cool Blue	15	8
2548SW0064	12/3	SJTW	50'	15.2 m	Cool Blue/Red	15	8
2548SW00HX	12/3	SJTW	50'	15.2 m	Cool Blue/Cool Green	15	8
2548SW0052	12/3	SJTW	50'	15.2 m	Dark Green/Yellow	15	8
2548SW0054	12/3	SJTW	50'	15.2 m	Lime Green/Red	15	8
2578SW000X	12/3	SJTW	50'	15.2 m	Cool Green	15	8
2548SW003V	12/3	SJTW	50'	15.2 m	Cool Orange/Cool Blue	15	8
2578SW000A	12/3	SJTW	50'	15.2 m	Cool Pink	15	8
2548SW0077	12/3	SJTW	50'	15.2 m	Cool Pink/Lime Green	15	8
2548SW0041	12/3	SJTW	50'	15.2 m	Red/White	15	8
2588SW0002	12/3	SJTW	50'	15.2 m	Yellow	15	6
2548SW0022	12/3	SJTW	50'	15.2 m	Yellow/Purple	15	8
550523**	12/3	SJTW	50'	15.2 m	Yellow/Black	15	6
25850002	12/3	SJTW	80'	24.4 m	Yellow	15	4
2549SW0064	12/3	SJTW	100'	30.5 m	Cool Blue/Red	15	4
2579SW000H	12/3	SJTW	100'	30.5 m	Cool Blue	15	4
2549SW0054	12/3	SJTW	100'	30.5 m	Lime Green/Red	15	4
2579SW000X	12/3	SJTW	100'	30.5 m	Cool Green	15	4
2549SW0052	12/3	SJTW	100'	30.5 m	Dark Green/Yellow	15	4
2549SW003V	12/3	SJTW	100'	30.5 m	Cool Orange/Cool Blue	15	4
2549SW0077	12/3	SJTW	100'	30.5 m	Cool Pink/Lime Green	15	4
2579SW000A	12/3	SJTW	100'	30.5 m	Cool Pink	15	4
2549SW0041	12/3	SJTW	100'	30.5 m	Red/White	15	4
2549SW0022	12/3	SJTW	100'	30.5 m	Yellow/Purple	15	4
2589SW0002	12/3	SJTW	100'	30.5 m	Yellow	15	4
2687SW0002	10/3	SJTW	25'	7.6 m	Yellow	15	6
26480064	10/3	SJTW	50'	15.2 m	Cool Blue/Red	15	4
26480054	10/3	SJTW	50'	15.2 m	Lime Green/Red	15	4
2688SW0002	10/3	SJTW	50'	15.2 m	Yellow	15	4
26490064	10/3	SJTW	100'	30.5 m	Cool Blue/Red	15	3
26490054	10/3	SJTW	100'	30.5 m	Lime Green/Red	15	3
2689SW0002	10/3	SJTW	100'	30.5 m	Yellow	15	3

*Black Plugs

**Product packaging is advertised in Meters